### UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUNAVUT	NOVA SCOTIA YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NEWFOUNDLAND AND LABRADOR
MANUFACTURERS NAME:	Swagelok Company		
MANUFACTURERS ADDRES		d, Solon, Ohlo 44139 USA	
PLANT LOCATIONS: Head		Road, Solon, Ohio 44139 USA (See	Attachment A)
		ED. CIRCLE ONE CATEGORY ONLY	IME OF THE STANDARD OF CONSTRUCTIO
Pipe fittings, including cosp     B Flenges: all flenges     C Valves: all flenges     C Valves: all fire yalves     D Expansion joints, flexible of     Strainers, filters, separation     Hessuring devices, including persons from the property of     C offilied capacity-raised pre	klings, taes, elbows, Ys, plu onnections, and hose seaer I, and sissem traps og pressure geuges, level g ssure tellal devicas accept	gs, unions, pipe caps, or reducers	ASME B31.1 for unlisted components, ASME B31.3 for unlisted components
bolers, pressure vessels, ; H Pressure retaining compon	epts that do not full total one	of the shows relenance	1
N Nuclear components: Clas	1 Cass 2 Cass 3	D, (Meeting AECS or ASME requirements)	1
SHOW MANUFACTURERS N	AME, TRADEMARK, OR L	OGO AS IT WILL APPEAR ON THE PRODU	CT TYPE OF CONSTRUCTION
Swa	agelok		PORCED D WILDED D WINDWORT X CAST D CTHER D DESCRISE OTHER
LIST OF SUPPORTING DOC	UMENTATION AND IDEN	IFICATION OF THE ACTUAL ITEMS TO BE	REGISTERED:
my knowledge represents the temperature ratings, and ide manufacture of these fittings or in part and has been verified.	of the end product do so e product for which regi- ntification markings are its regulated by a Qualiti fed by RSI	elemnity declare that the information conta stration is sought. The dimensions, mate in accordance with the herein named sta y Control Program which extends to each sea below suitable for	riels of construction, pressure ndards. I further declare that the a plant where fabrication occurs in whole that purpose and I make this colone.
declaration conscientiously	believing it to be true, an	d knowing that it is of the same force and	effect as if made under oath.
Signature of Declarer:	Lel Ville	_	
	50/00 210		
Declared before me at	Dian, Onio		S SPACE FOR THE
This 180' day of 1	JOUGU W	2020_ of	FICIAL SEAL
Commissioner of Oaths or Notary Public: (sign)	All All Seal to the r	and O	
		is space for Regulatory Authority use	
TN		validated after ten (10) years from the da	RESSURE LESSURE TO THE STATE OF
	_	8 F	RESSURE
CRN: 0A22318.5		(ER. a	No. 12
FIDE: 1214		ON NO	MA SCOTIA
High Pressure Fittings Notes bar) 45000psi @	- A479 316 (strain up to 200F;33400p	-nardened	2318.58
<ol> <li>All fittings shall be register.</li> <li>Each category shall be supforms and one copy of support</li> </ol>	ported with two Statutory D ting documentation.	ectaration Shood U	described
<ol> <li>The declaration shall be managed by the responsibility for the quality of</li> <li>Quality control programs at</li> </ol>	ade by the person having fu the and product.	a suthority and	1 d 1
at a mandmum interval of five CRN expires April	5) years.	170	Part ATIONS



Canadian Registration Number Submittal #SNOTRIK-FIT-2020 Category A: Swagelok High Pressure Fittings

# Attachment B. Scope for Swagelok High-Pressure Fittings (Category A)

Date: February 26, 2020

Page 1 of 2

This document represents the scope of the Swagelok High-Pressure Fittings covered by this submission for CRN approval. The High-Pressure Fittings were designed and evaluated in accordance with ASME B31.3-2018 Chapter IX for unlisted components.

#### **Summary Table**

Product Series / Tubing Size (inch)	Material (Standard)	Description	Form	Pressure Rating up to 200°F	Pressure Rating at 450°F
440 (1/4") 640 (3/8") 940 (9/16")	316 SS (ASTM A479)	High Pressure Tube Fitting	Unions, reducing unions, bulkhead unions, union elbows, union tees, caps, plugs, nuts,	0A22318.5 Technical Standa Boilers and Pre	ART OF CRI ards and Safety Author assure Vessels Safety
44M (1/4") 64M (3/8") 94M (9/16")		High Pressure Male Thread Connector	Unions		33,400 psi
440 to 44M, 64M (1/4") 640 to 44M, 64M (3/8") 940 to 64M, 94M (9/16")		High Pressure Tube Fitting to High Pressure Male Threaded Connectors	Straight Adapter		
44M to 441 (1/4") 64M to 641 (3/8") 94M to 941 (9/16")		High Pressure Male Thread to Coned Tube Stub	Straight Adapter		
440 to 641 (1/4") 640 to 941 (3/8") 940 to 641 (9/16")		High Pressure Tube Fitting to Coned Tube Stub Reducer	Straight Adapter		
441 (1/4") 641 (3/8") 941 (9/16")		Port Connector	Union		



Canadian Registration Number Submittal #SNOTRIK-FIT-2020 Category A: Swagelok High Pressure Fittings

#### **Product Illustration**



#### THIS IS PART OF CRN 0A22318.5

Date: February 26, 2020

Page 2 of 2

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

#### **Typical Product Characteristics:**

Additional options that do not affect pressure and/or temperature ratings may be made available within the scope of this approval. Examples of these would include the following:

- Special marking
- Special cleaning
- Wire drills

#### **Quality System**

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

#### References

Fitting Products - Sno-Trik Series section of Swagelok catalog "Medium- and High-Pressure Fittings, Tubing, Valves, and Accessories" MS-02-472 Rev. L

The above product catalog section does not represent the full scope of registration, but rather details some of the most common options for 316 SS high pressure fittings.

## **Attachment A. Swagelok Manufacturing Locations**

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

THIS IS PART OF CRN

0A22318.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

	Program		
Swagelok Company	Swagelok Company (Falon 1)		
29500 Solon Road	348 Bishop Road		
Solon, Ohio 44139	Highland Heights, Ohio 44143		
USA	USA		
Swagelok Company (Highland)	Swagelok Company (Falon 2)		
318 Bishop Road	358 Bishop Road		
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143		
USA	USA		
Swagelok Company (OFC)	Swagelok Company (HPF)		
29495 F.A. Lennon Drive	6050 Cochran Road		
Solon, Ohio 44139	Solon, Ohio 44139		
USA	USA		
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)		
26651 Curtiss Wright Parkway	6060 Cochran Road		
Willoughby Hills, Ohio 44092	Solon, Ohio 44139		
USA	USA		
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139		
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)		
29900 Solon Industrial Parkway	15400 Foltz Road		
Solon, Ohio 44139	Strongsville, Ohio 44119		
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man		