

July 5th, 2019

Dear Joanna Karpinski

Re: Reciprocal CRN Registration in Manitoba

Your application indicates that a CRN has been received in another Canadian Jurisdiction, and therefore your CRN has been registered in Manitoba as follows:

File Number: 39853

CRN:

0C21138.54

Scope:

See Scope of Registration, Attachment A & B

Manufacturer: SWAGELOK

Please find attached invoice for registration.

As indicated by the Regulatory Reconciliation and Cooperation Table and the Reconciliation Agreement for the Canadian Registration Number (CRN) for Pressure Equipment, a CRN issued in any Canadian Jurisdiction will be accepted for use in Manitoba.

In accordance with Steam and Pressure Plants Regulation and CSA B51, it is the manufacturer's responsibility to file a Manufacturers Data Report, including partial data reports, with our office, prior to shipping pressure equipment to Manitoba.

Please contact me directly via email at Cheryl.Lashek@gov.mb.ca for any questions or concerns.

Cheryl Lashek, P.Eng Director, ITSM Inspection and Technical Services Office of the Fire Commissioner 508 - 401 York Avenue, Winnipeg Manitoba R3C 0P8 T (204) 945-3507 | F (204) 948-2309



PV 09553 (06/16)

Technical Standards and Safety Authority 345 Carlingview Drive Toronto, Ontario M9W 6N9 www.lssa.org Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below



43004207000	STATUTORY DE Registration o		2*
I, Joel Feldma	an, Vice President of Engineering (Namo and Position, e.g. President, Plant I.	tanagar, Chief Engineer)	
of Swagelok		wings, wher Engineery	
01	(Name of Manufactur	er)	
	29500 Solon Road, Solon, Ohio 44139 USA	(440) 249 4600	/440) 040 5070
Located at	(Plant Address)	(440) 248-4600 (Talephone No.)	(440) 349-5970 (Fax No.)
and Pre	mnly declare that the fittings listed hereunder, which are su essure Vessels Regulation, comply with all of the requirem	ents of	0%-4000 E98
ASME	B31.1 for unlisted components, and ASME B31.3 for unlist (Title of recognized North America)	A DOS AND DANIES OF THE PROPERTY AND A SAME	
_	ecifies the dimensions, materials of construction, pressure/temp ot covered by the provisions of a recognized North America	erature ratings, identification markin	anufactured to comply with
pressure	e/temperature ratings and the basis for such ratings, the man	king of the fitting for identification	and service.
	e that the manufacture of these fittings is controlled by a qua which has been verified by the following authority, BSI and by this declaration, for which I seek registration, are category		ents of ISO 9001:2015 type fittings. In support of
	the following information and/or test data are attached as follows: 5 Certificate, Attachment A, Attachment B, Catalog Inform		nents
	(drawings, calculations, test re	parts, etc.)	
Declared befo	day of NOWINDER AD 20 18.	State	of Ohio
Commissions	Printed name) (Signature) Jamie L Ristau Resident Portage County Notary Public, State of Ohio Rily Commission Expires: 03/06/20	119 Scignature of	Declarer)
	FOR OFFICE USE	ONLY Technical	Boilers and
Technical Stan	by knowledge and belief, the application meets the requirement and safety Act, Boilers and Pressure Vessels Regulation in Category C		Pressure Vessels Salety Program
CRN:	OC21138.5	REGIST	A SERVICE AND A
Registered by:		C.R.N.: 0C21	138.5
Dated:	Jeb 22, 2013	Signed:	22 2010
OTE: This -	Tel 22 2020	Date: H.b. C	44019

For scope of registration see attached stamped documents: attachment A and By

Swagelok
Canadian Registration Number Submittal #60BALL-2018

Category C: Swagelok 60 Series Ball Valves

Date: January 22, 2019

Page 1 of 5

Attachment B: Scope for Swagelok 60 Series Ball Valves (Category C)

This document represents the scope of the 60 Series Ball Valves covered by this submission for CRN approval. The Swagelok 60 Series Ball Valves were designed and evaluated in accordance with ASME B31.1-2016 for unlisted components and ASME B31.3-2016 for unlisted components.

Product Pres Series Bea	Main	Pressure Bearing Material	Port Connections, Sizes*	Maximum Rated Pressure (Note 1)		Design Code
	Bearing Component			At 100°F	CAMPAGE AND	of Construction
		316SS (ASTM A479 or ASTM A351)	Swagelok Tube Fitting 1/4", 3/8" Female NPT 1/8", 1/4" Female ISO 1/4" Tube Butt Weld 1/4", 3/8" Pipe Butt Weld 1/4", 3/8" Tube Socket Weld 1/4", 3/8" Male VCO Fitting 1/4" Male VCR Fitting 1/4"	3000 psig (4 bolt body) 2500 psig (8 bolt body)	800 psig @450°F (4 bolt body) 200 psig@600°F (8 bolt body)	
62	Body	WCB Carbon Steel (ASTM A215)	Swagelok Tube Fitting 1/4", 3/8" Female NPT 1/8", 1/4" Tube Butt Weld 1/4", 3/8" Pipe Butt Weld 1/4", 3/8" Tube Socket Weld 1/4", 3/8"	3000 psig (4 bolt body) 2500 psig (8 bolt body)	800 psig @450°F (4 bolt body) 200 psig @600°F (8 bolt body)	
		Brass C36000 or C35600 (ASTM B16)	Swagelok Tube Fitting 1/4", 3/8" Female NPT 1/8", 1/4"	2000 psig	100 psig @400*F	
		Alloy C276 bar (ASTM B574) or CW-12MW Cast (ASTM A494)	Swagelok Tube Fitting 1/4", 3/8" Female NPT 1/4"	1500 psig	1470 psig @150*F	
		Alloy 400 N04400 (ASTM B164)	Swagelok Tube Fitting 1/4", 3/8" Female NPT 1/4"	1500 psig	1470 psig @150°F	
		Titanium Grade 4 UNS R50700 (ASTM B348)	Swagelok Tube Fitting 1/4", 3/8" Female NPT 1/4"	1500 psig	1380 psig @150°F	ASME B31.1 (Unlisted
CRN	IS PAI	316SS (ASTM A479 or ASTM A351)	Swagelok Tube Fitting 1/2", 3/4" Female NPT 3/8", 1/2" Female ISO 1/2" Tube Butt Weld 1/2" Pipe Butt Weld 1/2" Tube Socket Weld 1/2", 3/4" Pipe Socket Weld 1/2" Male VCO Fitting 1/2" Male VCR Fitting 1/2"	2500 psig (4 bolt and 8 bolt bodies) 3000 psig (welded bodies)	800 psig @450°F (4 bolt body) 1000 psig @850°F (8 bolt body) 100 psig @450°F (welded)	Components) and ASME B31.3 (Unlisted Components)
63	Body	WCB Carbon Steel (ASTM A216)	Swagelok Tube Fitting 1/2", 3/4" Female NPT 3/8", 1/2" Female ISO 1/2" Tube Butt Weld 1/2" Tube Socket Weld 1/2", 3/4" Pipe Socket Weld 1/2", 3/4"	2500 psig	800 psig @450°F (4 bolt body) 200 psig @800°F (8 bolt body)	
		Brass C36000 or C35600 (ASTM B16)	Swagelok Tube Fitting 1/4", 3/8" Female NPT 1/8", 1/4"	1500 psig	100 psig @400°F	
		Alloy C276 bar (ASTM B574) or CW-12MW Cast (ASTM A494)	Swagelok Tube Fitting 1/2" Female NPT 1/2"	1500 psig	1470 psig @150*F	
		Alloy 400 N04400 (ASTM B164)	Swagelok Tube Fitting 1/2" Female NPT 1/2"	1500 psig	1470 psig @150°F	
		Titanium Grade 4 UNS R50700 (ASTM B348)	Swagelok Tube Fitting 1/2" Female NPT 1/2"	1500 psig	1380 psig @150*F	

Swagelok
Canadian Registration Number Submittal #60BALL-2018
Category C: Swagelok 60 Series Ball Valves

Date: January 22, 2019 Page 2 of 5

roduct	Main Pressure	Main Pressure	Dest Consecutions Circuit	Maximum Rated Pressure (Note 1)		Design Code of	
Series	Bearing	Bearing Material	Bearing Port Connections, Sizes	At 100°F	At Max temp	Construction	
65	Body	316SS (ASTM A479 or ASTM A351)	Swagelok Tube Fitting 1" Female NPT 3/4", 1" Female ISO 3/4", 1" Pipe Butt Weld 3/4", 1" Tube Butt Weld 3/4", 1" Tube Socket Weld 1" Pipe Socket Weld 3/4", 1"	2500 psig (4 bolt and 8 bolt bodies) 3000 psig (Welded bodies)	800 psig @450°F (4 bolt body) 1000 psig @850°F (8 bolt body) 100 psig @450°F (welded)		
		WCB Carbon Steel (ASTM A216)	Swagelok Tube Fitting 1" Female NPT 3/4", 1" Female ISO 3/4", 1" Pipe Butt Weld 3/4", 1" Tube Butt Weld 3/4", 1" Tube Socket Weld 1" Pipe Socket Weld 3/4", 1"	2500 psig	800 psig @450°F (4 bolt body) 200 psig @800°F (8 bolt body)	18 PAR	
		Brass C36000 or C35600 (ASTM B16)	Swagelok Tube Fitting 1" Female NPT 3/4", 1"	1500 psig	100 psig @400°F		
		Alloy C276 bar (ASTM B574) or CW-12MW Cast (ASTM A494)	Female NPT 1*	1500 psig	1470 psig @150°F	Straubi & Safer	
		Alloy 400 N04400 (ASTM B164)	Swagelok Tube Fitting 1" Female NPT 1"	1500 psig	1470 psig @150°F		
		Titanium Grade 4 UNS R50700 (ASTM B348)	Female NPT 1*	1500 psig	1380 psig @150°F		
67 Bod	P-4	316SS (ASTM A479 or ASTM A351)	Swagelok Tube Fitting 1-1/2" Female NPT 1-1/4", 1-1/2" Female ISO 1-1/4" Pipe Butt Weld 1-1/2" Tube Butt Weld 1-1/2" Tube Socket Weld 1-1/4",1-1/2" Pipe Socket Weld 1-1/4", 1-1/2"	1500 psig (4 bolt body) 2000 psig (8 bolt body)	500 psig @450°F (4 bolt body) 500 psig @850°F (8 bolt body)	and ASME B31.3	
	67	Body	WCB Carbon Steel (ASTM A216)	Swagelok Tube Fitting 1-1/2" Female NPT 1-1/4", 1-1/2" Female ISO 1-1/4" Pipe Butt Weld 1-1/2" Tube Butt Weld 1-1/2" Tube Socket Weld 1-1/4",1-1/2" Pipe Socket Weld 1-1/4", 1-1/2"	2200 psig	800 psig @450"F (4 bolt body) 200 psig @300"F (8 bolt body)	
68	Body	316SS (ASTM A479 or ASTM A351)	Swagelok Tube Fitting 2" Female NPT 2" Female ISO 2" Pipe Butt Weld 2" Tube Butt Weld 2 Tube Socket Weld 2" Pipe Socket Weld 2"	1500 psig (4 bolt body) 2000 psig (8 bolt body)	500 psig @450°F (4 bolt body) 500 psig @850°F (8 bolt body)		
		WCB Carbon Steel (ASTM A216)	Swagelok Tube Fitting 2" Female NPT 2" Female ISO 2" Pipe Butt Weld 2" Tube Butt Weld 2 Tube Socket Weld 2" Pipe Socket Weld 2"	2200 psig (4 bolt body) 2000 psig (8 bolt body)	800 @450°F (4 bolt body) 200 psig @600°F (8 bolt body)		
62, 63, 65 (3-way)	Body	316SS (ASTM A479 or ASTM A351)	Swagelok Tube Fitting 1/4", 3/8", 1/2" Female NPT 1/8", 1/4",1/2", 1" Female ISO 1/4", 1/2, 3/4", 1"	1000 psig	800 psig @450°F		
67, 68 (3-way)	Body	316SS (ASTM A479 or ASTM A351)	Swagelok Tube Fitting 1-1/2" 2" Female NPT 1-1/4", 1-1/2", 2" Female ISO 1-1/4", 1-1/2", 2" Tube Socket Weld 1-1/4", 1-1/2", 2" Pipe Socket Weld 1-1/4", 1-1/2", 2"	500 psig	500 psig @450°F		

Swagelok

Canadian Registration Number Submittal #60BALL-2018 Category C: Swagelok 60 Series Ball Valves

Date: January 22, 2019 Page 3 of 5

* Fractional port connection sizes shown. Equivalent metric size ranges are also in scope, and have the same pressure/temperature ratings

Note 1: Pressure ratings shown are the maximum possible for the combination of valve series and body material. Seat and flange seals will affect ratings; please refer to product literature.

Product Illustration




THIS IS PART OF CRN OC 21138. 5
Technical Standards & Salety Anthonly Bollers & Pressure Vessels Safety Program


Configurations

The pressure retaining components of the 60 Series ball valve bodies can be categorized into three main types of assemblies based on the method used to attach the flanges to the body:

8 bolt







The 4 bolt type assemblies are available in all body materials.


The 8 bolt type assemblies are available in Stainless Steel and Carbon Steel only.

The welded assemblies are available in Stainless Steel only.

Swagelok

Canadian Registration Number Submittal #60BALL-2018 Category C: Swagelok 60 Series Ball Valves Date: January 22, 2019 Page 4 of 5

60 Series 3-Way Valves



3-Way valves are available in the 4-bolt type assembly and Stainless Steel material only.

Product Options:

The product options listed below affect pressure and/or temperature ratings shown in the above Summary Table, but in all cases the ratings are less than those shown in the table.

Flange Seal Material Options


Fluorocarbon, FKM Buna N Buna C Ethylene Propylene Neoprene Grafoil PTFE

Stem Seal Material Options

PTFE, virgin
Fluorocarbon, FKM
Buna C
Ethylene Propylene
Grafoil
PEEK (virgin, coated, or reinforced)

Seat Material Options

PTFE, virgin
PTFE, reinforced
PTFE, carbon glass filled
PEEK (virgin, coated, or reinforced)
UHMWPE
Inconel X-750



Additional options that do not increase the pressure and/or temperature ratings may be made available within the scope of this approval. Examples of these would include the following:

Handle options
Actuators (e.g. pneumatic, electric)
Panel mounting
Low dead space inserts

All of the above options, those that affect pressure and/or temperature ratings and those that do not, are within the scope of this approval.

Swagelok

Canadian Registration Number Submittal #60BALL-2018 Category C: Swagelok 60 Series Ball Valves

Date: January 22, 2019 Page 5 of 5


Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog-does not represent the full scope of registration, but rather details some of the most common options.

60 Series Ball Valve Catalog MS-01-146, Rev U



Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Company A.G. (European Technology Center) St. GallerstraBe 84 Lachen, Switzerland 8853 Switzerland
Swagelok Limited Ballafletcher Road Fromode M4 4RA sle of Man	THIS IS PART OF

