



June 3rd, 2019

Dear Joanna Karpinski

Re: Reciprocal CRN Registration in Manitoba

Your application indicates that a CRN has been received in another Canadian Jurisdiction, and therefore your CRN has been registered in Manitoba as follows:

File Number: 39652
CRN: 0C20864.54
Scope: V2, V3, & V5 Series Manifolds
Manufacturer: Swagelok Company

Please find attached invoice for registration.

As indicated by the Regulatory Reconciliation and Cooperation Table and the Reconciliation Agreement for the Canadian Registration Number (CRN) for Pressure Equipment, a CRN issued in any Canadian Jurisdiction will be accepted for use in Manitoba.

In accordance with Steam and Pressure Plants Regulation and CSA B51, it is the manufacturer's responsibility to file a Manufacturers Data Report, including partial data reports, with our office, prior to shipping pressure equipment to Manitoba.

Please contact me directly via email at Cheryl.Lashek@gov.mb.ca for any questions or concerns.

Cheryl Lashek, P.Eng
Director, ITSM
Inspection and Technical Services
Office of the Fire Commissioner
508 - 401 York Avenue, Winnipeg Manitoba R3C 0P8
T (204) 945-3507 | F (204) 948-2309



Technical Standards and Safety Authority
 345 Carlingview Drive
 Toronto, Ontario M9W 6N9
 www.tssa.org



STATUTORY DECLARATION Registration of Fittings

I, Joel Feldman, Vice President, Engineering
(Name and Position, e.g. President, Plant Manager, Chief Engineer)

of Swagelok Company
(Name of Manufacturer)

Located at 29500 Solon Road, Solon, Ohio 44139 USA (440) 248-4600 (440) 349-5970
(Plant Address) (Telephone No.) (Fax No.)

do solemnly declare that the fittings listed hereunder, which are subject to the **Technical Standards and Safety Act**, Boilers and Pressure Vessels Regulation, comply with all of the requirements of ASME B31.1 for unlisted components where applicable, and ASME B31.3 for unlisted components where applicable
(Title of recognized North American Standard)
 which specifies the dimensions, materials of construction, pressure/temperature ratings, identification marking the fittings and service;

or are not covered by the provisions of a recognized North American standard and are therefore manufactured to comply with _____ as supported by the attached data which identifies the dimensions, material of construction, pressure/temperature ratings and the basis for such ratings, the marking of the fitting for identification and service.

I further declare that the manufacture of these fittings is controlled by a quality system meeting the requirements of ISO 9001:2015 which has been verified by the following authority, BSI

The items covered by this declaration, for which I seek registration, are category C. Valves type fittings. In support of this application, the following information and/or test data are attached as follows:
ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents
(drawings, calculations, test reports, etc.)

Declared before me at Solon in the State of Ohio
 the 09th day of August AD 2018.

Commissioner for Oaths: Jamie L Ristau
(Printed name)
Jamie L Ristau
(Signature)
 Jamie L. Ristau
 Resident Portage County
 Notary Public, State of Ohio
 My Commission Expires: 03/06/2019

Joel Feldman
(Signature of Declarer)

FOR OFFICE USE ONLY

To the best of my knowledge and belief, the application meets the requirements of the **Technical Standards and Safety Act**, Boilers and Pressure Vessels Regulation, and CSA Standard B51 and is accepted for registration in Category C

REGISTERED

C.R.N.: OC20864.5

Signed: [Signature]

Date: Nov 18, 2018

CRN: OC20864.5
 Registered by: [Signature]
 Dated: Nov. 18, 2018

NOTE: This registration expires on: Nov. 18, 2028

Scope of registration:

Attachment B. Scope for Swagelok V Series Manifold Valves (Category C)

Product Scope

This document represents the scope of Swagelok® V Series Manifold Valves covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1 for unlisted components and ASME B31.3 for unlisted components.

Summary Table

Product Series	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections and Sizes	Maximum Rated Pressure (psig)		Design Code of Construction
				@ 100°F	@ Max Temp	
V2	Standard Body	316SS (ASTM A479)	Swagelok Tube Fitting 1/2", 12MM Female NPT 1/4", 1/2"	6000	1715 @ 1200°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
			Flange (MSS)	6000	3030 @ 1000°F	
V2	Compact Body	316SS (ASTM A479)	Male NPT 1/2", 3/4" Female NPT 1/2", 3/4" Female NPT 1/4" (vent)	6000	1715 @ 1200 °F	
V3	Standard Body	316SS (ASTM A479)	Swagelok Tube Fitting 1/2", 12MM Female NPT 1/2"	6000	1715 @ 1200 °F	
			Flange (MSS)	6000	3030 @ 1000°F	
V3	Compact Body	316SS (ASTM A479)	Male NPT 1/2", 3/4" Female NPT 1/2", 3/4" Female NPT 1/4" (vent)	6000	1715 @ 1200 °F	
V5	Standard Body	316SS (ASTM A479)	Swagelok Tube Fitting 1/2", 12MM Female NPT 1/8", 1/4", 1/2"	6000	1715 @ 1200 °F	
			Flange (MSS)	6000	3030 @ 1000°F	

THIS IS PART OF
CRN 0C 20864.5
 Technical Standards & Safety Authority
 Boilers & Pressure Vessels
 Safety Program

Product Illustration

V2 Series Manifold Valves

Standard Body



Flange Body




Compact Body



V3 Series Manifold Valves

Standard Body




Compact Body




V5 Series Manifold Valves

Standard Body – One Bleed Valve



Standard Body – Two Bleed Valves



Product Options:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

Valve Design

Small Bonnet Valve – actuator threads are wetted
Large Bonnet Valve – actuator threads are non-wetted

Valve Packing Material

Virgin Polytetrafluoroethene (PTFE) – standard
Grafoil – high temperature option

Flange Seal Materials

Fluorocarbon FKM
Virgin Polytetrafluoroethene (PTFE)
Reinforced Polytetrafluoroethene (PTFE)
Grafoil

MSS Flange Fasteners

Standard Hex Head Bolt
Long Stud with Hex Nut
Short Hex head Bolt

Eccentric Flanges

Swagelok Tube Fitting
Female NPT
Pipe Butt Weld

Concentric and Eccentric Pipe Nipples

Stainless Steel
Carbon Steel



Quality System

Swagelok Company's quality system complies with the requirements of BS EN ISO 9001:2015. Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate. The V Series Manifold Valves are manufactured at a Swagelok Company location in Solon, Ohio.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options. See Swagelok's Instrument Manifold Systems Catalog MS-02-445, R2

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (Highland) 318 Bishop Road Highland Heights, Ohio 44143 USA	Swagelok Company (Falon 2) 358 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (OFC) 29495 F.A. Lennon Drive Solon, Ohio 44139 USA	Swagelok Company (HPF) 6050 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Atlantic) 26651 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Snow Metal) 6060 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC) 29900 Solon Industrial Parkway Solon, Ohio 44139	Swagelok Company (Strongsville) 15400 Foltz Road Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Company A.G. (European Technology Center) St. GallerstraBe 84 Lachen, Switzerland 8853 Switzerland
Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man	

