UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUNAVUT	NOVA SCOTIA YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NEWFOUNDLAND AND LABRADOR		
MANUFACTURERS NAME:	Swagelok Company				
MANUFACTURERS ADDRESS					
PLANT LOCATIONS: Headou	parters: 29500 Solo	n Road, Solon, Chio 44139 USA (See	Attachment A)		
CATEGORY OF FITT	INGS TO BE REGISTER	RED. CIRCLE ONE CATEGORY ONLY	TOTALE OF THE STANDARD OF COASTRUCTION		
A Flanges: all flanges C Valves: all fire valves D Expansion joints, flexible con E Strainers, filters, separators, i F Measuring devices, including pressure transmitters G Certified capacity-rated press boilers, pressure vessels, pip H Pressure retaining component	nections, and hose asser- and steam traps pressure gauges, level g ture refer devices accept ling and fusible plugs ts that do not fall into on-	auges, sight glasses, levels, or	ASME B31.1 for unlisted components, ASME B31.3 for unlisted components		
SHOW MANUFACTURERS NAM SWQ	gelok gelok	OGO AS IT WILL APPEAR ON THE PROD	FORGED WELDED D WROUGHT X CAST D STREET D DESCRIBE OTHER		
DECLARATION:		nent B, Catalog Information and other St			
Joel Feldman, Vice President, Enginersponsibility for the quality of my knowledge represents the temperature ratings, and identifications of these fittings is or in part and has been verified.	the end product do so product for which registration markings are a regulated by a Qualit d by ESI lieving it to be true, and I I nable to get	elemnly declare that the information cont stration is sought. The dimensions, met in accordance with the herein named st by Control Program which extends to ear as being suitable for discovering that it is of the same force ar and a motary Signaster & H	andards, I further declare that the chiplant where fabrication occurs in whole or that purpose and I make this solemn and effect as if made under cath.		
Commissioner of Osths					
or Notary Public: (sign)	April 22, 20				
	Affix Official seal to the				
This		is space for Regulatory Authority use			
	egistration must be re	velidated after ten (10) years from the d	9%		
CRN: 0C22506.5	er :		Newfoundland Labrador		
FID#: 1214			Service NL		
BV series Bleed valve	s and P series I	Purge	Registered 0622506 50		
valves series.			Date 20/01/22		
All fittings shall be registered Each collegey shall be support			Engineering and Inspection Services		
Each category shall be supporting forms and one copy of supporting	g documentation.		0111		
3. The declaration shall be made	Registered by				
responsibility for the quality of the 4. Quality control programs shall	be resubmitted for valid	fation	UNDER THE AUTHORITY OF THE PUBLIC SAFETY ACT AND		
at a maximum interval of five (6) CRN expires June 1	years.		THE BOILER, PRESSURE VESSEL AND COMPRESSED GAS REGULATIONS		



Canadian Registration Number Submittal Category C: Swagelok Bleed Valves and Purge Valves

THIS IS PART OF CRN 0C22506.5 Technical Standards and Safety Authority Boilers and Pressure Vessels Saferyate: May 29,2020

Page 1 of 2

Attachment B: Scope for Swagelok BV Series Bleed Valves and P Series Purge Valves (Category C)

This document represents the scope of the Swagelok BV Bleed Valves and P Purge Valves covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1-2018 for unlisted components and ASME B31.3-2018 for unlisted components.

Summary Table

				Maximum Rate	ed Pressure	
Series		Main Pressure Bearing Material (Standard)	Port Connections, Sizes	(psig)		Design Code
	Pressure Bearing Component			At -65 to 100°F (except Carbon Steel)	At max temperature	of Construction
BV Body, Stem	316 SS (ASTM A479)	Male NPT 1/8", 1/4", 3/8", 1/2"	10,000	6085 @ 850°F		
		Male ISO 1/4",1/2"				
		Male SAE 1/4",1/2"	4,568	4568 @ 400°F		
BV Body, Stem	1018 Carbon Steel (ASTM A108)	Male NPT 1/8", 1/4", 3/8", 1/2"	10,000 @ -20 to 100°F	8630 @ 375°F		
		Male ISO 1/4",1/2"				
		Male SAE 1/4",1/2"	4,568 @ -20 to 100°F	4568 @ 375°F		
P Body, Cap	316 SS (ASTM A479)	Female & Male NPT 1/8", 1/4", 3/8", 1/2"	4000	2500 @ 600°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	
		Male ISO 1/8"				
		Swagelok Tube Fitting 1/8", 1/4", 3/8", 1/2", 6MM, 8MM				
		Male SAE 1/4", 1/2"	4000	2850 @ 400°F		
P Body, Cap		ndy, Cap 12L14 Carbon Steel (ASTM A108)	Female & Male NPT 1/8", 1/4", 3/8", 1/2"	3000 @ -20 to 100°F	3000 @ 250°F	
			Male SAE 1/4", 1/2"			
	Body, Cap		Male ISO 1/8"			
			Swagelok Tube Fitting 1/8", 1/4", 3/8", 1/2", 6MM, 8MM			



Canadian Registration Number Submittal
Category C: Swagelok Bleed Valves and Purge Valves

THIS IS PART OF CRN

0C22506.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

Date: May 29,2020 Page 2 of 2

Product		Main Pressure Bearing Material (Standard)	Port Connections, Sizes	Maximum Rated Pressure (psig)		Design Code
Series				At -65 to 100°	At max temperature	Of Construction
P Body, Cap		Brass y, Cap	Male NPT 1/8", 1/4", 1/2"		740 @ 400°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted
			Male ISO 1/8"	3000		
			Swagelok Tube Fitting 1/8", 1/4", 3/8", 1/2", 6MM			
			Swagelok Tube Fitting 8MM	2322		
	Body, Cap		Swagelok Tube Fitting 3/8"	2200		
			Swagelok Tube Fitting 1/2"	2100		
			1/8" FNPT	3000	640 @ 400°F	Components)
			1/4" FNPT	3000	660 @ 400°F	
			3/8" FNPT	2600	520 @ 400°F	
			1/2" FNPT	2400	480 @ 400°F	
			Male SAE 1/4", 1/2"	2284	297 @ 400°F	

Product Illustrations

BV Series Bleed Valves



P Series Purge Valves



Typical Product Characteristics:

Some of the product options listed below could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

BV Series Bleed Valves

Handles Vent Tubes

P Series Purge Valves

Ball Material (316SS standard, PTFE optional)

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

BV Bleed Valves and P Purge Valves Catalog MS-01-62, Rev N

THIS IS PART OF CRN 0C22506.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man