UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUNAVUT	NOVA SCOTIA YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NOF FITTING DESIGNS NEWFOUNDLAND AND LABRADOR
MANUFACTURERS NA	ME: Swagelok Company		
MANUFACTURERS ADD	DRESS: 29500 Solon Road	d Solon Obio 44130 USA	
PLANT LOCATIONS:	leadquarters: 29500 Solor	n Road, Solon, Ohio 44139 USA (See At	took
CATEGORY O	F. FITTINGS TO BE REGISTER	ED, CIRCLE ONE CATEGORY ONLY	TRUE OF THE STANDARD OF CONSTRUCTION
A Pipa fittings, including B Flanges: all flanges C Valves: all line valves D Expansion joints, flaxis E Strainers, filters, sepai F Measuring devices, inspects pressure transmitters G Certified capacity-rate boillers, pressure vess H Pressure retaining con	couplings, tees, elbows, Ys, plus ble connections, and hose assen- rators, and steam traps cluding pressure gauges, level ga d pressure retial devices accepts els, piping and fusible plugs reponents that do not tall into one	igs, unions, pipe caps, or reducers mbiles: all types suges, sight glasses, levels, or able as primary over pressure protection on s of the above categories	Rubber Products Manufacturers (ARPM) Hose Handbook
N Nuclear components:	Class 1 Class 2 Class 3	(Meeting AECB or ASME requirements)	
0	agelok	OGO AS IT WILL APPEAR ON THE PRODUCT	FORGED D WELDED D WROUGHT D CAST D OTHER X DUBGRIBLE OTHER PTFE CORE
LISY OF SUPPORTING	DOCUMENTATION AND IDENT	TIFICATION OF THE ACTUAL ITEMS TO BE RE	GIEVEDED.
esponsibility for the quality knowledge represent my knowledge represent emperature ratings, and manufacture of these fith or in part and has been the contract of the co	ts the product for which regis didentification markings are it tings is regulated by a Quality verified by RSI	lemnly declare that the information contains stration is sought. The dimensions, materia in accordance with the herein named stand, y Control Program which extends to each p	is of construction, pressure ards, I further declare that the lant where fabrication occurs in whole
	411.7	all	nect as it made under oath.
ignature of Declarer:	20100		
nis day o	'scal due to CO'	notary signature on is	SPACE FOR THE
ammissioner of Oathe	- September 17	, 2020	
	Thi	is space for Regulatory Authority use	ESSECTION A. TOTAL
	inis registration must be rev	validated after ten (10) years from the date	of acceptage
CRN: 0D22750.5	<u> </u>	Print.	Newfoundland Labrador
FID#: 1214		F., .	Service NL
Notes: 1. All fittings shall be region. 2. Each category shall be forms and one copy of su	es PTFE hose asserting of the Manufacture of the Ma	facturer. Engineeration Req	istered OP 32.750.50 20/11/13 ineering and Inspection Services istered by 1
3 The declaration shall be responsibility for the quality control program at a maximum interval of	e made by the person having full by of the and product.	Ill authority and	INDER THE AUTHORITY OF THE



Canadian Registration Number Submittal
Category D Crimped Swagelok ST series PTFE Hose

THIS IS PART OF CRN 0D22750.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

September 1, 2020 Page 1 of 2

Attachment B: Scope of Registration for Crimped Swagelok ST series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex ST series hose and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

Summary Table

ST	ST Maximum Pressure (psig)					
series Hose Size	At Minimum Temp. (-65°F)	Room temperature (0°-100°F)	At Maximum Temp. (400°F)	Pressure Retaining Material	End Connections and Sizes	Design Code of Construction
1/8"	3000	3000	2550			
1/4"	3500	3500	3250	3250 Core Smooth Bore PTFE Braid	Swagelok Tube Fitting [SL SM] 1/8" – 2" (3 – 50mm) Male & Female NPT Tapered Pipe Fitting [PM, PF] 1/8" – 2"	
3/8"	3000	3000	2350	Synthetic Fiber Braid & 304 SS Braid Reinforcement	Male & Female ISO/BSP Tapered (ISO 7) Pipe Threads [MT, FT] 1/4" – 1" Male 37° JIC & Female 37° JIC with female swivel nut [AN, AS] 1/4" – 2"	Association for Rubber Products Manufacturers
1/2	1800	1800	1800	Cover Silicone cover End Connections 316 SS	Tube Butt Welds [TB] 1/2" – 1" Male & Female VCO O-ring Face seal Fitting [VF, VM] 1/8" - 2"	(ARPM) Hose Handbook
3/4	1250	1250	1250	Crimp on Collar 300 series SS	Male & Female VCR Metal Gasket Face seal Fitting [RF, RM] 1/8"- 2" Female ISO/BSP Parallel Threads (ISO 228) [FS] 1/4" – 1"	
1"	1000	1000	1000			



Canadian Registration Number Submittal
Category D Crimped Swagelok ST series PTFE Hose

THIS IS PART OF CRN

0D22750.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program


September 1, 2020 Page 2 of 2

Product Description

The Swagelok ST series hose is a virgin PTFE-lined hose with a fiber braid reinforcement and 304 stainless steel reinforcement with silicone cover. The exceptions are the 1/8-inch nominal size hose does not have the fiber braid and the 1 inch nominal size is constructed with two stainless steel braids and no fiber braid. All ST series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).

Configurations

All end connection inserts are crimped onto the hose using crimp collars.



Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

Cover Options

- Armor guard Interlocking, flexible 302 stainless steel.
- Fire jacket Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard Helical HDPE plastic

Tag and Marking Options

- Mat tag Polyester tag with customer-specified text
- Lanyard tag Stainless steel tag with customer-specified text

End Connection Seals or Sealants Options

- VCO O-rings
- Pipe Thread ends thread sealant

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

THIS IS PART OF CRN 0D22750.5

Technical Standards and Safety Authority

Attachment A. Swagelok Manufacturing Locations Boilers and Pressure Vessels Safety Program

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man