# UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

New Brunswick Nunavut	Nova Scotia Yukon	Prince Edward Island Northwest Territories	Newfoundland and Labrador
	1e:Swagelok Company		
Manufacturers Add	ress:29500 Solon Road, S	iolon, Ohlo 44139-3492	
Plant Locations: He	adquarters: 29500 Solon Ro	oad, Solon, Ohlo 44139-3492 (See Attachment	
A Rico fittings including	of Fittings to be regis	tered. Circle one Category only	Title of the Standard of
B Flances: all flances		s, plugs, unions, pipe caps, or reducers	Construction
C Valves; all line valves			British Standards Institution
E Strainers filters sens	ible connections, and hose trators, and steam traps	assemblies: all types	
F Measuring devices, in	cluding pressure gauges, k	evel gauges, sight glasses, levels, or pressure	
l transmitters		cceptable as primary over pressure protection (	
Dollers, pressure vess	els, piping and fusible plug		on
H Pressure retaining co	mponents that do not fall in	to one of the above categories	
N Nuclear components:	Class 1 Class 2 C	lsss 3 🗆 , (Meeting CNSC or ASME requireme	ents)
Show Manufacturers	Name, Trademark, or	Logo as it will appear on the product	Type of Construction
			Forged o Welded o Wrought B
Suga	adala		Cast o Other o Describe other;
OWO	agelok		
		tification of the actual Items to be regis	etered: attachment B, Catalog Information
rny knowledge represer ratings, and identification fittings is regulated by a verified by as	e quality of the end produte the product for which on markings are in accomp Quality Control Program at makings that it is of the state	registration is sought. The dimensions, in registration is sought. The dimensions, in adance with the herein named standards. In which extends to each plent where fabric being suitable for that purpose and I main assume force and effect as if made under	and being the person having full authority on contained in this form is true to the best of naterials of construction, pressure temperature if further declare that the manufacture of these cation occurs in whole or in part and has been ke this solemn declaration conscientiously roath.  ELEANOR L DUKE official Seal State of Ohio My Comm. Expires May 27, 2027
	This registration mus	This space for Regulatory Authority use, st be revalidated after ten (10) years from the d	ale of arreniance
CRN: 0C16304.5	Rev1	and the first state of the first	
			6500
FID#: 1214			
Notes:			
	istered in the name of the Manu	facturer. / Nort	twest Territories
Each Category shall be and one copy of suppor	supported with two Statutory E rting documentation,	Deceration rooms	CISTERED
1 The Declaration shall b	e made by the person having fu	ull authority and	THE ALITHOHILY UP
	selity of the end product.	THE BOIL	EH AND PRESSOR
Scope: CRN renewa	ns shall be resubmitted for valid al. K Series Pressure	Regulators \	ESSEL ACT. Sect La - Flores Rev.2
Jack KPR, KC	Y, KCM, KLF, KHF, I	KCP, KPP, KPF,	C16304. ST Dies Para Rev 2
KHP, KHR, KBP, KEV-Piston KSV)	B, KCB, KPB, KHB,	and the same	
ASME B31.1, B31.3	code of construction	. SIGNE	2 18 5 2023
	5th, 2033 (DGallant)	DATÉ -	Sarring

# Attachment B. Scope for Swagelok K Series Pressure Regulators (Category C)

#### **Product Scope**

This document represents the scope of the K Series Pressure Regulators covered by this submission for CRN approval. The Swagelok K Series Pressure Regulators were designed and evaluated in accordance with ASME B31.1 for unlisted components and ASME B31.3 for unlisted components.

## **Summary Table**

	ure	Mate		ı	Design Code of Construction			
Product Series Main Pressure Bearing Component	Main Pressure Bearing Material	Port Connections and Sizes	At ambient temperature			At maximum temperature		
			Inlet	Outlet	Inlet	Outlet		
		Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	6000 psi @ 100 °F	500 psi @ 100 °F	3600 psi @ 392 °F	500 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
			Tube Stub 1/4" x .035 VCR Gland no nuts 1/4" VCR rotatable female 1/4" VCR rotatable male 1/4"	3600 psi @ 100 ⁰F	500 psi @ 100 ºF	3600 psi @ 392 ºF	500 psi @ 392 ºF	
KPR	Body	Brass (UNS C67500 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 <sup>0</sup> F	500 psi @ 100 ⁰F	3600 psi @ 392 ⁰F	500 psi @ 392 <sup>0</sup> F	
		Alloy 400 (UNS N04400 / ASTM B164)						
		Alloy C-276 (UNS N10276 / ASTM B574)						
		Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	6000 psi @ 100 °F	500 psi @ 100 °F	3600 psi @ 392 °F	500 psi @ 392 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
	Rody	Brass (UNS C67500 / ASTM B138) Alloy 400 (UNS N04400 / ASTM B164) Alloy C-276 (UNS N10276 / ASTM B574)	Female NPT 1/4"	3600 psi @ 100 <sup>0</sup> F	500 psi @ 100 <sup>0</sup> F	3600 psi @ 392 °F	500 psi @ 392 <sup>0</sup> F	
KCY	Войу							
КСМ	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 <sup>0</sup> F	500 psi @ 100 ⁰F	3600 psi @ 392 <sup>0</sup> F	500 psi @ 392 <sup>0</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KLF	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 ⁰F	250 psi @ 100 °F	3600 psi @ 392 <sup>⁰</sup> F	250 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

	ure nt		Maximum Rated Pressure					
Product Series Main Pressure Bearing Component		Main Pressure Bearing	Port Connections and Sizes	At ambient temperature		At maximum temperature		Design Code of Construction
<b>.</b>	Mair Co	Material		Inlet	Outlet	Inlet	Outlet	
KHF	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/2"	3600 psi @ 100 °F	250 psi @ 100 ºF	3600 psi @ 392 ºF	250 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КСР	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/8"	3600 psi @ 100 ºF	1500 psi @ 100 <sup>0</sup> F	3600 psi @ 392 ºF	1500 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KPP	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	6000 psi @ 100 ºF	3000 psi @ 100 ºF	6000 psi @ 392 ºF	2975 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KPF	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/2"	6000 psi @ 100 ºF	4000 psi @ 100 ºF	6000 psi @ 392 ºF	4000 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KHP	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	10000 psi @ 100 ºF	8000 psi @ 100 ºF	10000 psi @ 392 ºF	8000 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KHR	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	10000 psi @ 100 ºF	8000 psi @ 100 ºF	10000 psi @ 212 ºF	8000 psi @ 212 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КВР		Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4" Tube Stub 1/4" x .035 VCR Gland no nuts 1/4" VCR rotatable female 1/4" VCR rotatable male 1/4"	500 psi @ 100 <sup>0</sup> F	500 psi @ 100 <sup>0</sup> F	500 psi @ 392 <sup>0</sup> F	500 psi @ 392 <sup>0</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KUF	Body	Brass (UNS C67500 / ASTM B138) Alloy 400 (UNS N04400 / ASTM B164) Alloy C-276 (UNS N10276 / ASTM B574)	Female NPT 1/4"	500 psi @ 100 <sup>0</sup> F	500 psi @ 100 <sup>0</sup> F	500 psi @ 392 <sup>0</sup> F	500 psi @ 392 <sup>0</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

	ure nt		Maximum Rated Pressure					
Product Series Main Pressure Bearing Component		Main Pressure Bearing	Port Connections and Sizes	At ambient temperature		At maximum temperature		Design Code of Construction
	Mair E Co	Material		Inlet	Outlet	Inlet	Outlet	
KFB	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/2"	250 psi @ 100 °F	250 psi @ 100 ºF	250 psi @ 392 ºF	250 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КСВ	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/8"	375 psi @ 100 ºF	375 psi @ 100 <sup>0</sup> F	375 psi @ 392 <sup>0</sup> F	375 psi @ 392 <sup>0</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КРВ	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3000 psi @ 100 °F	3000 psi @ 100 ºF	2975 psi @ 392 <sup>0</sup> F	2975 psi @ 392 <sup>0</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КНВ	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	8000 psi @ 100 °F	8000 psi @ 100 °F	8000 psi @ 212 ºF	8000 psi @ 212 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KEV (diaphr agm)	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 ºF	500 psi @ 100 ºF	3600 psi @ 392 ºF	500 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KEV (piston)	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 °F	3000 psi @ 100 ºF	3600 psi @ 392 ºF	2975 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KSV	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 ºF	500 psi @ 100 <sup>0</sup> F	3600 psi @ 392 <sup>0</sup> F	500 psi @ 392 <sup>0</sup> F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

#### **Product Illustration**



## **Typical Product Characteristics**:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

PCTFE seat material PEEK seat material

Some of the product options listed below do not affect the pressure-temperature ratings shown in the Summary Table. All of the following options are within the scope of this registration:

ASTM G93 Level-E cleaned Swagelok SC-11 cleaned Handle Type (e.g. knob, thumbwheel, etc) Panel Mounting

#### **Quality System**

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2015. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate. The K Series Pressure Regulators are manufactured at a Swagelok Company locations in Solon, Ohio and Tromode, Isle of Man, British Isles.

#### References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

• K Series Pressure Regulator Catalog MS-02-230, Rev Q