UMFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUNAVUT

NOVA SCOTIA YUKON PRINCE EDWARD ISLAND NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: Swagelok Company		
MANUFACTURERS ADDRESS: 29500 Solon Road, Solon, O	hio 441391154	
PLANT LOCATIONS: Headquarters: 29500 Solon Road, Sol	lon. Ohio 44139 USA (See Att	achment A)
CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE	ONE CATEGORY ONLY	TITLE OF THE SYMMOMED OF CONSTRUCTION
A Pipe fittings, including couplings, tess, albows, Ys, plugs, unions, p B Planges: all flanges C Valves: all line valves D Expansion joints, flaxible connections, and hose essemblies: all typ E Strahers, filters, separators, and steam traps F Massuring devices, including pressure gauges, level gauges, sight operature transmitters G Certified capacity-sited pressure raisef devices acceptable as prima bollers, pressure vessels, piping and fusible plugs H Pressure retaining components that do not fall into one of the above N Muclear components: Class 1	pea glasses, levels, or ry over pressure protection on a categories	ASME B31.1 and ASME B31.3 (for unlisted components)
HOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT V	WILL APPEAR ON THE PRODUCT	TYPE OF CONSTRUCTION
Swagelok		PORGED O WELDED O WROUGHT)[CAST O OTHER O DESCRIPTION OTHER
LIST OF BUPPORTING DOCUMENTATION AND IDENTIFICATION OF	OF THE ACTUAL ITEMS TO BE REC	
y knowledge represents the product for which registration is so		in this form is true and to the best of
enufacture of these fittings is regulated by a Quality Control Pro in part and has been verified by BSI claration conscientiously believing it to be true, and knowing the posture of Declarar:	to with the herein named standan ogram which extends to each plar as being suitable for that that it is of the same force and elie	of construction, pressure ts. I further declare that the where febrication occurs in whole purpose and I make the
anufacture of these fittings is requisted by a Quality Control Proin part and has been verified by BSI incleration conscientiously believing it is be true, and knowing the greature of Declarer: Control Proint	with the herein named standars plan which extends to each plan as being suitable for the	of construction, pressure ts. I further declare that the where febrication occurs in whole purpose and I make the
anufacture of these fittings is requisited by a Quality Control Pro- in part and has been verified by. 351 cleration conscientiously believing it to be true, and knowing the greature of Declarer: clered before me at 5000. On 0 day of November AD 2017 commissioner of Oeths Notary Public: (sign) (Affix Official seal to the right)	pe with the herein named standan ogram which extends to each plar as being suitable for that that it is of the same force and elle to be the same force and elle to be the same to be the	of construction, pressure ts. I further declare that the I where fabrication occurs in whole purpose and I make the sound ct as if made in S P AICT
anufacture of these fittings is requisited by a Quality Control Pro- in part and has been verified by BSI claration conscientiously believing. It is be true, and knowing the greature of Declarer: clared before me at SOLOD ONLO is SOLOD ONLO is SOLOD ONLO immissioner of Oeths Notary Public: (sign) (Affect Official seal to the right) This registration must be revealed after RN: OC18486.2	with the herein named standard or with the herein named standard or the same force and effect that it is of the same force and effect in the same force in the same force in the same same same same same same same sam	of construction, pressure ts. I further declare that the it where fabrication occurs in whole purpose and I make the commod as if made units S P AICI I A E
Notary Public: (sign) (Affix Official seal to the right) This space for Re This registration must be reveiledeted after	with the herein named standard open which extends to each plan as being suitable for that that it is of the same force and effect in the same Lister County OFFIC in the same Lister County OFFIC in the same Lister County Public, State of Ohle Commission Explans 04/05/2011 Significant County use or ten (10) years broth the date of the Newforthickend Listerador	of construction, pressure ts. I further declare that the I where fabrication occurs in whole purpose and I make his commod at as If made in S P Alor I A E A Company A Compa



Attachment B. Scope of Registration for Swagelok MN Series Process Monoflanges (Category C)

Product Scope

This document represents the scope of Swagelok MN Series Process Monoflanges covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1 and ASME B31.3 as unlisted components.

Summary Table

Code of construction is 831.3 only UK

The below table holds true for:

- MN02 Outside Screw & Yoke Series
- MN03 Integral Screwed-Bonnet Needle Valve Series, and
- MN04 Bolted-Bonnet Needle Valve (Primary Bloc) Series

Body Material/ Specification	Configuration	ASME Class	Flange Size	Minimum Temperature	Maximum Working Pressure (psig) ¹	
					At 70°F	At 300°F
F316/F316L ASTM A182	Block Valve	150	1/2 in. (DN 15)			
		150	3/4 in. (DN 20)			
	Block and Bleed Valve	300/600 900/1500 2500	1 in. (DN 25)	-58°F	6000	4660
	Double Block and Bleed		1 1/2 in. (DN 40)			
	and bleed 2500	2 in. (DN 50)				

- 1) Maximum temperature: PTFE Packing 400°F, Graphite Packing 850°F,
- 2) All seat and seal combinations
- 3) All flange types: RF smooth, RF serrated, and RTJ

KEITH RUDOLF, P.Eng.

DESIGN SURVEY ENGINEER


- 4) Outlet connection: 1/2 in. female NPT, Monoflange wafer (thru holes)
- 5) Bleed connection: 1/4 in. female NPT, 1/2 in. female NPT, or none

ህያ(ብ
SAFETY CODES ACT - PROVINCE OF ALBERTA
REGISTRATION OF FITTINGS
REGISTRATION NO. 0 C 1 8 4 8 6 . 2
DWG. NO. or CAT. NO. Attachment B
TYPE OF FITTINGS Valve Assemblies
APR 1 1 2018 INITIALS Model Readely

Date


As Noted

"See Acceptance Letter for the comments and/or conditions of registration"




Canadian Registration Number Submittal Swagelok Submission #MN(SS)-2017

Product Drawings/Configurations



Double Block and Bleed Valve



Typical Product Characteristics:

The list below shows examples of product options which do not affect the pressure-temperature ratings shown in the above Summary Table. All of the following options are within the scope of this registration:

- Bar Handles (available for block valves and bleed valves)
- Handwheel Handles (for block valves)
- Antitamper bleed valve
- Sour gas service

Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2008. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

Special Ordering Instructions

None

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

Swagelok Process Interface Valves MS-02-340, R10