UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

New Brunswick Nunavut	Nova Scotia Yukon	Prince Edward Northwest Ter		wfoundland and Labrador			
Manufacturers Nar	ne;Swagelok Company						
Manufacturers Add	dress: 29500 Solon Road, Sol	lon, Ohio 44139-3492					
Plant Locations: He	eadquarters: 29500 Solon Roa	id, Solon, Okio 44139-34	92 (See Attachment A)				
A Pipe fittings, including	y of Fittings to be registents couplings, tees, elbows, Ys,	red. Circle one Cate	gory only	Title of the Standard of			
B Flanges: all flanges		, progs, unions, pipe cap	s, or reducers	Construction			
C Valves: all line valve	s xible connections, and hose a	acception, all house		British Standards Institution			
E Strainers, filters, ser	parators, and steam trans						
F Measuring devices, i transmitters	including pressure gauges, lev	el gauges, sight glasses	, levels, or pressure				
G Certified capacity-rat	led pressure relief devices acc	eptable as primary over	pressure protection on				
boilers, pressure ves	sels, piping and fusible plugs						
	components that do not fall into						
N Nuclear components	s: Class 1 Class 2 Cla	ass 3 🗆 , (Meeting CNSC	or ASME requirements)				
Show Manufacture	rs Name, Trademark, or I	ogo as it will appear	on the product	Type of Construction			
C				Forged D Welded D Wrought 8 Cast D Other D			
Simo	≫olopu.			Describe other:			
O 49.	ageion						
List of supporting	documentation and ident	ification of the actua	I Itame to be register				
ISO 9001: 2015	Quality System Cer	tificate Support	Documente: Atta	chment B, Catalog Information			
100 0001. 2010	adding Oydicin Oci	illicate, oupport	Documents. Atta	chinem b, Catalog information			
L							
Declaration;							
Jay Nordholl , Vice President,	Engineering (see note 3) e	mployed by Swagelo	k Company a	nd being the person having full authority contained in this form is true to the best of			
and responsibility for	the quality of the end produ	uct do solemnly declar	e that the information of	contained in this form is true to the best of			
ratings and identifica	tion markings are in accord	registration is sought.	ine dimensions, mate	orials of construction, pressure temperature ther declare that the manufacture of these			
fittings is regulated by	a Quality Control Program	which extends to each	ch plant where fabricati	on occurs in whole or in part and has been			
verified by BSI	89	being suitable for that	t purpose and I make t	his solemn declaration conscientiously			
believing it to be true,	and knowing that it is of the	e same force and effe	ct as if made under oa	th.			
Signature of Declarer	- SNeile	HI					
Declared before pre	C 1 A						
1714	100	2113	STATE OF THE PARTY	ELEANOR L DUKE			
		- alone	S THE	space/fauthe Official Seal State of Ohio			
Commissioner of Oat		10.	E POLICE ON A	ky Comm. Expires			
Or Notary Public: (sig	n) francis	ALVU	9	May 27, 2027			
	(Affix Official seal to the	e right)					
		This space for Regula	tory Authority use.				
0046304	This registration mus	st be revalidated after ter	(10) years from the page	o posentance.			
CRN: 0C16304	.5 Revi		ER CO	S			
FID#: 1214			NOVAS	WITA PA			
Notes:	The state of the s		Date Aug.	35/33 V			
	registered in the name of the Manu	ufacturer.	CRN OCU	304.58Rev. I			
-	be supported with two Statutory [
and one copy of sur	porting documentation.		Dwg. as de	escribed			
	all be made by the person having for equality of the end product.	ull authority and	Signed				
	Commence and the commence of t	dation	~	6 1 6			
Scope: CRN rene	rams shell be resubmitted for valle wal, K Series Pressure	Regulators	PA _1_0				
KHP KHR KRP	KCY, KCM, KLF, KHF, KFB, KCB, KPB, KHB,	KEV-Diaph	Pa	irt (S)			
LKEV-Piston, KSV	1. 15 plant locations.		The state of the s	GULA			
ASME B31.1, B3	1.3 code of construction	1.					
CKN expires Aug	.15th, 2033 (DGallant)						

Attachment B. Scope for Swagelok K Series Pressure Regulators (Category C)

Product Scope

This document represents the scope of the K Series Pressure Regulators covered by this submission for CRN approval. The Swagelok K Series Pressure Regulators were designed and evaluated in accordance with ASME B31.1 for unlisted components and ASME B31.3 for unlisted components.

Summary Table

	ure	Mate		ı	Design Code of Construction			
Product Series Main Pressure Bearing Component	Main Pressure Bearing Material	Port Connections and Sizes	At ambient temperature			At maximum temperature		
			Inlet	Outlet	Inlet	Outlet		
		Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	6000 psi @ 100 °F	500 psi @ 100 °F	3600 psi @ 392 °F	500 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
			Tube Stub 1/4" x .035 VCR Gland no nuts 1/4" VCR rotatable female 1/4" VCR rotatable male 1/4"	3600 psi @ 100 ⁰F	500 psi @ 100 ºF	3600 psi @ 392 ºF	500 psi @ 392 ºF	
KPR	Body	Brass (UNS C67500 / ASTM A479)		3600 psi @ 100 ⁰ F	500 psi @ 100 ⁰F	3600 psi @ 392 ⁰F	500 psi @ 392 ⁰ F	
		Alloy 400 (UNS N04400 / ASTM B164)	Female NPT 1/4"					
		Alloy C-276 (UNS N10276 / ASTM B574)						
		Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	6000 psi @ 100 °F	500 psi @ 100 °F	3600 psi @ 392 °F	500 psi @ 392 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KCY Body	Rody	Brass (UNS C67500 / ASTM B138)	Female NPT 1/4"	3600 psi @ 100 ºF	500 psi @ 100 ⁰ F	3600 psi @ 392 ⁰ F	500 psi @ 392 ⁰ F	
	Войу	Alloy 400 (UNS N04400 / ASTM B164)						
		Alloy C-276 (UNS N10276 / ASTM B574)						
КСМ	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 ⁰ F	500 psi @ 100 ⁰F	3600 psi @ 392 ⁰ F	500 psi @ 392 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KLF	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 ⁰F	250 psi @ 100 °F	3600 psi @ 392 ^⁰ F	250 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

	ure nt		Maximum Rated Pressure					
Product Series Main Pressure Bearing Component		Main Pressure Bearing	Port Connections and Sizes	At ambient temperature		At maximum temperature		Design Code of Construction
.	Mair Co	Material		Inlet	Outlet	Inlet	Outlet	
KHF	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/2"	3600 psi @ 100 °F	250 psi @ 100 ºF	3600 psi @ 392 ºF	250 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КСР	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/8"	3600 psi @ 100 ºF	1500 psi @ 100 ⁰ F	3600 psi @ 392 ºF	1500 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KPP	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	6000 psi @ 100 ºF	3000 psi @ 100 ºF	6000 psi @ 392 ºF	2975 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KPF	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/2"	6000 psi @ 100 ºF	4000 psi @ 100 ºF	6000 psi @ 392 ºF	4000 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KHP	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	10000 psi @ 100 ºF	8000 psi @ 100 ºF	10000 psi @ 392 ºF	8000 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KHR	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	10000 psi @ 100 ºF	8000 psi @ 100 ºF	10000 psi @ 212 ºF	8000 psi @ 212 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КВР		Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4" Tube Stub 1/4" x .035 VCR Gland no nuts 1/4" VCR rotatable female 1/4" VCR rotatable male 1/4"	500 psi @ 100 ⁰ F	500 psi @ 100 ⁰ F	500 psi @ 392 ⁰ F	500 psi @ 392 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KUF	Body	Brass (UNS C67500 / ASTM B138) Alloy 400 (UNS N04400 / ASTM B164) Alloy C-276 (UNS N10276 / ASTM B574)	Female NPT 1/4"	500 psi @ 100 ⁰ F	500 psi @ 100 ⁰ F	500 psi @ 392 ⁰ F	500 psi @ 392 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

	ure nt		Maximum Rated Pressure					
Series Series Pres Hoon Bear		Main Pressure Bearing	ure Port Connections and ing Sizes	At ambient temperature		At maximum temperature		Design Code of Construction
	Mair E Co	Material		Inlet	Outlet	Inlet	Outlet	
KFB	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/2"	250 psi @ 100 °F	250 psi @ 100 ºF	250 psi @ 392 ºF	250 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КСВ	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/8"	375 psi @ 100 ºF	375 psi @ 100 ⁰ F	375 psi @ 392 ⁰ F	375 psi @ 392 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КРВ	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3000 psi @ 100 °F	3000 psi @ 100 ºF	2975 psi @ 392 ⁰ F	2975 psi @ 392 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
КНВ	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	8000 psi @ 100 °F	8000 psi @ 100 °F	8000 psi @ 212 ºF	8000 psi @ 212 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KEV (diaphr agm)	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 ºF	500 psi @ 100 ºF	3600 psi @ 392 ºF	500 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KEV (piston)	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 °F	3000 psi @ 100 ºF	3600 psi @ 392 ºF	2975 psi @ 392 ºF	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
KSV	Body	Stainless Steel (UNS S31600 / ASTM A479)	Female NPT 1/4"	3600 psi @ 100 ºF	500 psi @ 100 ºF	3600 psi @ 392 ⁰ F	500 psi @ 392 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

Product Illustration



Typical Product Characteristics:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

PCTFE seat material PEEK seat material

Some of the product options listed below do not affect the pressure-temperature ratings shown in the Summary Table. All of the following options are within the scope of this registration:

ASTM G93 Level-E cleaned Swagelok SC-11 cleaned Handle Type (e.g. knob, thumbwheel, etc) Panel Mounting

Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2015. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate. The K Series Pressure Regulators are manufactured at a Swagelok Company locations in Solon, Ohio and Tromode, Isle of Man, British Isles.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

• K Series Pressure Regulator Catalog MS-02-230, Rev Q