UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUNAVUT	NOVA SCOTIA YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NEWFOUNDLAND AND LABRADOR
MANUFACTURERS NAME:	Swagelok Company	The second secon	
MANUFACTURERS ADDRESS		i, Solon, Ohio 44139 USA	
PLANT LOCATIONS: Headq	uarters: 29500 Solon	Road, Solon, Ohio 44139 USA (See	Artachment A)
CATEGORY OF FITT	INGS TO BE REGISTER	ED. CIRCLE ONE CATEGORY ONLY	TITLE OF THE SYMPLAND OF CONSTRUCTION
A Pipe fittings, including couplist B Flanges: all flanges C Valves: all tine valves D Expansion joints, flexible con E Strainers, filters, asparators, F Measuring devices, including pressurfs transmitters	ngs, tees, elbows, Ys, ploy mections, and hose assen and steam traps pressure gauges, level ga	gs, unions, pipe caps, or reducers	ASME B31.1 for unlisted components, ASME B31.3 for unlisted components
boilers, pressure vessels, pig	soulg eldicut bna pnic		
H Pressure retaining componer			
N Nuclear components: Class	1 Class 2 Class 3	D. (Meeting AECB or ASME requirements)	
Swa		AS II WILL APPEAR ON THE PROD	TYPE OF CONSTRUCTION PORGED O WELDED O WROUGHT OF CAST O THER O DESCRIBE OTHER
LIST OF SUPPORTING DOCUM	MENTATION AND IDENT	IFICATION OF THE ACTUAL ITEMS TO B	E REGISTERED:
		ent B, Catalog Information and other Se	- Commence
responsibility for the quality of ny knowledge represents the temperature ratings, and ident manufacture of these fittings is or in part and has been verified	the end product do sol product for which regis diffication markings are it regulated by a Quality d by ESI	emnly declare that the information cont tration is sought. The dimensions, mat in accordance with the herein named st control Program which extends to each	andards. I further declare that the chiplant where fabrication occurs in whole or that purpose and I make this release.
	111211		onoce as it made diluter Calif.
Signature of Declarer:	tool (. Table		
Declared before me at	Unable to ge	t a notary signature H	IS SPACE FOR THE
This day of Commissioner of Oeths or Notary Public: (sign)	or seal dule to April 22, 202 (Amx Official seal to the re	o Covid- 19 situation ^r	FICIAL SEAL
This		s space for Regulatory Authority use	
CRN: 0C22506.5 FID#: 1214	registration must be rev	relidated after ten (10) years from the d	PRESSURE VEST
BV series Bleed valve	_		July 17/2
valvae carios	as and P series F		17/20
valves series. 1. All fittings shall be registered		Purge CRN OC	2014 17/20 O



Canadian Registration Number Submittal Category C: Swagelok Bleed Valves and Purge Valves

THIS IS PART OF CRN 0C22506.5 Technical Standards and Safety Authority Boilers and Pressure Vessels Saferyate: May 29,2020

Page 1 of 2

Attachment B: Scope for Swagelok BV Series Bleed Valves and P Series Purge Valves (Category C)

This document represents the scope of the Swagelok BV Bleed Valves and P Purge Valves covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1-2018 for unlisted components and ASME B31.3-2018 for unlisted components.

Summary Table

				Maximum Rate	ed Pressure	
Product Product Series Bo		Main Pressure Bearing Material (Standard)	Port Connections, Sizes	(psig)		Design Code
	Pressure Bearing Component			At -65 to 100°F (except Carbon Steel)	At max temperature	of Construction
BV Body, Stem	316 SS (ASTM A479)	Male NPT 1/8", 1/4", 3/8", 1/2"	10,000	6085 @ 850°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	
		Male ISO 1/4",1/2"		000 1		
		Male SAE 1/4",1/2"	4,568	4568 @ 400°F		
BV Body, Stem	1018 Carbon Steel (ASTM A108)	Male NPT 1/8", 1/4", 3/8", 1/2"	10,000 @ -20 to 100°F	8630 @ 375°F		
		Male ISO 1/4",1/2"				
		Male SAE 1/4",1/2"	4,568 @ -20 to 100°F	4568 @ 375°F		
P Body, Cap	316 SS (ASTM A479)	Female & Male NPT 1/8", 1/4", 3/8", 1/2"	4000	2500 @ 600°F		
		Male ISO 1/8"				
		Swagelok Tube Fitting 1/8", 1/4", 3/8", 1/2", 6MM, 8MM				
		Male SAE 1/4", 1/2"	4000	2850 @ 400°F		
P Body, Cap	12L14 Carbon	Female & Male NPT 1/8", 1/4", 3/8", 1/2"	0000	0000		
		Male SAE 1/4", 1/2"				
	Body, Cap		Male ISO 1/8"	3000 @ -20 to 100°F	3000 @ 250°F	
			Swagelok Tube Fitting 1/8", 1/4", 3/8", 1/2", 6MM, 8MM			



Canadian Registration Number Submittal
Category C: Swagelok Bleed Valves and Purge Valves

THIS IS PART OF CRN

0C22506.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

Date: May 29,2020 Page 2 of 2

Product	Main Pressure	Main Pressure Bearing Material (Standard)	Port Connections, Sizes	Maximum Rated Pressure (psig)		Design Code
Series	Bearing Component			At -65 to 100°	At max temperature	Of Construction
P Body, C		Brass C36000	Male NPT 1/8", 1/4", 1/2"		740 @ 400°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted
			Male ISO 1/8"	3000		
			Swagelok Tube Fitting 1/8", 1/4", 3/8", 1/2", 6MM			
			Swagelok Tube Fitting 8MM	2322		
	Body, Cap		Swagelok Tube Fitting 3/8"	2200		
		(ASTM B16)	Swagelok Tube Fitting 1/2"	2100		
			1/8" FNPT	3000	640 @ 400°F	Components)
			1/4" FNPT	3000	660 @ 400°F	
			3/8" FNPT	2600	520 @ 400°F	
			1/2" FNPT	2400	480 @ 400°F	
			Male SAE 1/4", 1/2"	2284	297 @ 400°F	

Product Illustrations

BV Series Bleed Valves



P Series Purge Valves



Typical Product Characteristics:

Some of the product options listed below could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

BV Series Bleed Valves

Handles Vent Tubes

P Series Purge Valves

Ball Material (316SS standard, PTFE optional)

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

BV Bleed Valves and P Purge Valves Catalog MS-01-62, Rev N

THIS IS PART OF CRN 0C22506.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man