UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

PRINCE EDWARD ISLAND

NOVA SCOTIA

NEW BRUNSWICK

NEW BRUNBARCK MUNAVUT	NOVA SCOTIA YUKON		EDWARD ISLAND IMEST TERRITORIES	NEWFOUNDLAND AND LABRADOR		
MANUFACTURERS NAME:	Swagelok Company					
MANUFACTURERS ADDRESS	29500 Solon Road, Solon, Ohio 44139 USA					
PLANTLOCATIONS: Headq	uarters: 29500 Solon	Road, Solon	Ohio 44139 USA (See	Attachment A)		
CATEGORY OF FIT	INGS TO BE REGISTER	D. CIRCLE OF	E CATEGORY ONLY	TITLE OF THE STANDARD OF CONSTRUCTION		
A Pipe fittings, isolading coupli ill Planges: all flanges C Valenc: all fire valves D Expansion joints, flanbis cor E Strainers, filters, separators,	enections, and hose assert	shine: all types		ASME B31.1 for unlisted components, ASME B31.3 for		
F Measuring devices, including pressure transmitters. 6 Coeffed empely-rained pres- bother, pressure vessels, pi H Pressure retailing compone M Noticer components: Class	pressure gauges, level ge sure relief devices accepte plag and fusible plugs ris that do not full into any 1 [1] Class 2 [1] Olyse 3 (ble on primary of of the shove on D. (Meeting AE	wer pressure protection on tegerles CB or ASME requirements)	unlisted components		
SHOW MANUFACTURERS MA	ME TRADEMARK OR LO	JW TI EA OD	LAPPEAR ON THE PROD			
Swa	gelok	•		SUBCOMME CHARTS IN AMOUGHL IN		
LIST OF SUPPORTING DOCU	MENTATION AND IDENT	FICATION OF	THE ACTUAL ITEMS TO B	E REGISTERED:		
my knowledge represents the emperature ratings, and iden manufacture of these littings i or in part and has been verifie	f the end product do sole product for which regist diffication markings are in a regulated by a Quality of by BSI	emnly declare tretion is sough a accordance Control Progr	that the information cont ht. The dimensions, mat with the herein named am which extends to eac as being suitable fi it is of the same force an	i being the person having full authority and ained in this form is true and to the best of arials of construction, pressure andards, I further declare that the chiplant where fabrication occurs in whole or that purpose and I make this solemn at effect as If made under oath. ISSPACE FOR THE		
mia 3rd day of C	AD JOOK TO	2019		FICIAL SEAL		
Commissioner of Outris	1 (10	0				
or Notery Public: (sign)	(Affix Official seel to the ric	Mex	199	NILINIAN/LIT		
			ristory Authority use	NUNAVUI		
This	registration must be ray	alidated after	on (10) sates from the d	ate of screptage and		
CRN: 0A22314.5			Nuñavut	Pressure Vessels Act		
FIDE: 1214	_		REGISTERED			
Alloy 600 (ASTM B16	66, B564) Tube Fitti	ings.Note: I	for	1		
.B166 N06600 materia	al the annealed bar	a de la companya de l	CRN OA 22	314, SN		
All families shall be registrated Each category shall be supp	f in this trainle of the Manufi orbed with two Statutory De	acturer.	Date Huy	14, 2020		
forms and one copy of supports 3. The declaration shall be made	ng documentation.			16 1-		
responsibility for the quality of the	he end product.		Signed	atlebad Loduc		
4. Quality control programs also at a maximum interval of the (5	all be resubmitted for valida	resubmitted for validation Chie Puters Cos				
CRN expires April	3, 2030 - DG			AND THE PARTY OF T		
			Territorial	Registration Fee		



This document represents the scope of Swagelok Inconel Alloy 600 Tube Fittings covered by this submission for CRN approval. These Swagelok Tube Fittings have been evaluated in accordance with ASME B31.3 for unlisted components and ASME B31.1 for unlisted components.

Summary Table

wagelok

0A22314.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

	Material (Standard)		Maximum Allowable Working Pressure		Program
Product Description		Port Connections and			Design Code of
or Series		Sizes	Up to 100°F	At maximum temperature	Construction
and Adapter (ASTM I		Swagelok End Connection 1/4, 3/8, 1/2 inch	See Table below	See Table below	ASME B31.1 (Unlisted Components)
		6mm, 10mm, 12mm			ASME B31.3 (Unlisted Components)
	Alloy 600	NPT Male 1/16 - 1 inch	11 000 – 5300 psig	8800 - 4240 psig @ 900°F (482°C)	ASME B31.1 (Unlisted Components)
	ASTM B564)		11 000 – 5300 psig	3300 - 1590 psig @ 1000°F (537°C)	ASME B31.3 (Unlisted Components)
		NPT Female 1/16 - 1 inch	6700 – 4400 psig	5360 - 3520 psig @ 900°F (482°C)	ASME B31.1 (Unlisted Components)
			6700 – 4400 psig	2010 - 1320 psig @ 1000°F (537°C)	ASME B31.3 (Unlisted Components)


Alloy 600 Swagelok Tube Fitting Pressure Rating Table

	Maximum Allowable Working Pressure				
Swagelok End Connection Size	Up to 100°F	At maximum temperature 900°F (482°C) ASME B31.1	At maximum temperature 1000°F (537°C) ASME B31.3		
1/4	10 200 psig	5814 psig	3570 psig		
3/8	6500 psig	3705 psig	2275 psig		
1/2	5100 psig	2907 psig	1785 psig		
6mm	670 bar	381 bar	234 bar		
10mm	380 bar	216 bar	133 bar		
12mm	310 bar	176 bar	108 bar		



Product Description

Swagelok Fittings are furnished in a variety of configurations and shapes (straight, elbow, tee or cross). Swagelok Fittings consist of at least one Swagelok End – a proprietary two-ferrule mechanical-grip design. The table below, as well as the "Configurations" section, covers a variety of other end connections.






THIS IS PART OF CRN

0A22314.5


Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Configurations

1. Unions.



2. Male and Female connectors / adapters.



NPT Male Connectors

Female Connectors

February 6, 2020 Page 3 of 3

Product Options:

Some of the product options listed below affect the pressure-temperature ratings in the "Scope of Registration" section above, but in all cases the pressure ratings are the same or less than those shown in the Summary Table on page 1.

- Tapered pipe thread (NPT) sealant:
 - o Curable resin with PTFE
 - PTFE tape
- Bored through fittings
- Plastic ferrules, (Nylon, Teflon, PEEK)

Additional options that do not affect pressure and/or temperature ratings may be made available within the scope of this approval. Examples of these would include the following:

- Special marking
- Special cleaning
- Wire drills
- bulkhead configurations
- Snubbers/frits and orifice plates

All of the above options, those that affect pressure and/or temperature ratings and those that do not, are within the scope of this approval.

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015.

Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

THIS IS PART OF CRN

0A22314.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options.

- Gaugeable Tube Fittings and Adapter Fittings MS-01-140, Rev Y
- Swagelok Tubing Data Sheet MS-01-107, Rev N

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

THIS IS PART OF CRN

0A22314.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

	Program		
Swagelok Company	Swagelok Company (Falon 1)		
29500 Solon Road	348 Bishop Road		
Solon, Ohio 44139	Highland Heights, Ohio 44143		
USA	USA		
Swagelok Company (Highland)	Swagelok Company (Falon 2)		
318 Bishop Road	358 Bishop Road		
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143		
USA	USA		
Swagelok Company (OFC)	Swagelok Company (HPF)		
29495 F.A. Lennon Drive	6050 Cochran Road		
Solon, Ohio 44139	Solon, Ohio 44139		
USA	USA		
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)		
26651 Curtiss Wright Parkway	6060 Cochran Road		
Willoughby Hills, Ohio 44092	Solon, Ohio 44139		
USA	USA		
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139		
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)		
29900 Solon Industrial Parkway	15400 Foltz Road		
Solon, Ohio 44139	Strongsville, Ohio 44119		
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man		