

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
NUNAVUT

NOVA SCOTIA
YUKON

PRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: <u>Swagelok Company</u>	
MANUFACTURERS ADDRESS: <u>29500 Solon Road, Solon, Ohio 44139-3492</u>	
PLANT LOCATIONS: <u>Headquarters: 29500 Solon Road, Solon, Ohio 44139-3492 (See Attachment A)</u>	
CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY	
A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers B Flanges: all flanges C Valves: all line valves D Expansion joints, flexible connections, and hose assemblies: all types E Strainers, filters, separators, and steam traps F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs H Pressure retaining components that do not fall into one of the above categories I Nuclear components: Class 1 <input type="checkbox"/> Class 2 <input type="checkbox"/> Class 3 <input type="checkbox"/> (Meeting AECB or ASME requirements)	TITLE OF THE STANDARD OF CONSTRUCTION ASME B31.3 Chapter IX, for unlisted components where applicable
SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT	
	TYPE OF CONSTRUCTION FORGED <input type="checkbox"/> WELDED <input type="checkbox"/> WROUGHT <input type="checkbox"/> CAST <input type="checkbox"/> OTHER <input type="checkbox"/> DESCRIBE OTHER:
LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED: Attachment A, Attachment B, Support Documents, Catalog Information, ISO 9001:2008 Quality System Certificate Items To Be Registered: Swagelok IPT Series Valves	

DECLARATION:

I, David H. Peace (see note 3) employed by Swagelok Company and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by The British Standards Institution as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.



Signature of Declarer: [Signature]
Declared at: Solon, Ohio
This is the _____ day of January AD 2016
Commissioner of Claims
of Notary Public: (Sign) James R. Rustell
(Affix Official seal to the right)

THIS SPACE FOR THE OFFICIAL SEAL
James L. Riddis
Resident Portago County
Notary Public, State of Ohio
My Commission Expires: 03/06/2018


This space for Regulatory Authority use

This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: 0G18171 5

FID#: 1214

Notes:
 1. All fittings shall be registered in the name of the Manufacturer.
 2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
 3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
 4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.


 REGISTERED
 UNDER THE AUTHORITY OF
 THE BOILER AND PRESSURE
 VESSEL ACT.
 C.R.N. 0G18171 5
 SIGNED [Signature]
 DATE March 29 2016

5/6300

Attachment B1: Scope of CRN Registration for Swagelok IPT Series Check Valves (Category C)

This document represents the scope of the Swagelok IPT Series Check Valve covered by this submission for CRN approval. The Swagelok IPT Series Check Valves were designed and evaluated in accordance with ASME B31.3 Chapter IX, for unlisted components where applicable.

Summary Table

Product Description or Series	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections and Sizes	Maximum Rated Pressure		Design Code of Construction
				At ambient temperature	At maximum temperature	
CV (soft seat)	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	14,700 @ 250F	ASME B31.3 Chapter IX (For Unlisted Components Where Applicable)
CV (dual seat)	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	14,700 @ 250F	
CV (ball seat)	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	13,900 @ 650F	
CV (soft seat)	Body	ASTM A479	Female NPT 3/4", 1"	10,000 @ 100F	9,800 @ 250F	
CV (dual seat)	Body	ASTM A479	Female NPT 3/4", 1"	10,000 @ 100F	9,800 @ 250F	
CV (ball seat)	Body	ASTM A479	Female NPT 3/4", 1"	10,000 @ 100F	9,300 @ 650F	
CV (soft seat)	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16", 3/4", 1"	20,000 @ 100F	19,600 @ 250F	
CV (dual seat)	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16", 3/4", 1"	20,000 @ 100F	19,200 @ 250F	
CV (ball seat)	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16", 3/4", 1"	20,000 @ 100F	18,600 @ 650F	

Product Illustration



THIS IS PART OF
 CRN 0C18171.5
 Technical Standards & Safety Authority
 Boilers & Pressure Vessels
 Safety Program

Typical Product Characteristics

Some product options could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. An example of this would be optional body seal materials.

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. An example of this would be different poppet springs.

Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2008. In support of this, Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729 and HSB Registration Services Certificate of Registration Number HQ-Q-4, which apply to all locations listed on the certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

- Medium and High Pressure Valves, Fittings and Tubing Catalog MS-02-472



Attachment B2: Scope of CRN Registration for Swagelok IPT Series Double Block and Bleed Valves (Category C)

This document represents the scope of the Swagelok IPT Series Double Block and Bleed Valve covered by this submission for CRN approval. The Swagelok IPT Series Double Block and Bleed Valves were designed and evaluated in accordance with ASME B31.3 Chapter IX, for unlisted components where applicable.

Summary Table

Product Description or Series	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections and Sizes	Maximum Rated Pressure		Design Code of Construction
				At ambient temperature	At maximum temperature	
DB (ball-needle-ball)	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	14,700 @ 250F	ASME B31.3 Chapter IX (For Unlisted Components Where Applicable)
DB (needle-needle-needle)	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	14,700 @ 250F	
DB (ball-needle-ball)	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16"	15,000 @ 100F	14,700 @ 250F	
DB (needle-needle-needle)	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16"	20,000 @ 100F	19,600 @ 250F	

Product Illustration



Double Block & Bleed Valves

THIS IS PART OF
CRN 0C18171.5
Technical Standards & Safety Authority
Pressure & Pressure Vessels
Safety Program

Typical Product Characteristics

Some product options could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. An example of this would be optional body seal materials.

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. An example of this would be different handles.

Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2008. In support of this, Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729 and HSB Registration Services Certificate of Registration Number HQ-Q-4, which apply to all locations listed on the certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

- Medium and High Pressure Valves, Fittings and Tubing Catalog MS-02-249




Attachment B3: Scope of CRN Registration for Swagelok IPT Series Needle Valves (Category C)

This document represents the scope of the Swagelok IPT Series Needle Valve covered by this submission for CRN approval. The Swagelok IPT Series Needle Valves were designed and evaluated in accordance with ASME B31.3 Chapter IX, for unlisted components where applicable.

Summary Table

Product Description	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections and Sizes	Maximum Rated Pressure		Design Code of Construction
				At ambient temperature	At maximum temperature	
NVT	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	14,700 @ 250F	ASME B31.3 Chapter IX (For Unlisted Components Where Applicable)
NVT	Body	ASTM A479	Female NPT 3/4", 1"	10,000 @ 100F	9,800 @ 250F	
NVT	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16"	30,000 @ 100F	29,400 @ 250F	

Product Illustration



Typical Product Characteristics

Some product options could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. An example of this would be optional body seal materials.

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. An example of this would be different handles.

Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2008. In support of this, Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729 and HSB Registration Services Certificate of Registration Number HQ-Q-4, which apply to all locations listed on the certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

- Medium and High Pressure Valves, Fittings and Tubing Catalog MS-02-249

