UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS NEW BRUNSWICK **NOVA SCOTIA** PRINCE EDWARD ISLAND NEWFOUNDLAND AND LABRADOR NUNAVUT YUKON NORTHWEST TERRITORIES MANUFACTURERS NAME: Swagelok Company MANUFACTURERS ADDRESS: 29500 Solon Road, Solon, Ohio 44139 USA PLANT LOCATIONS: Headquarters: 29500 Solon Road, Solon, Ohio 44139 USA (See Attachment A) CATEGORY OF FITTINGS TO BE REGISTERED, CIRCLE ONE CATEGORY ONLY TITLE OF THE STANDARD OF CONSTRUCTION A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers B Flanges: all flanges ASME B31.1 for unlisted Valves: all line valves components where Expansion joints, flexible connections, and hose assemblies: all types E Strainers, filters, separators, and steam traps applicable, ASME B31.3 F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or for unlisted components prossure transmitters G Contified capacity-rated pressure relief devices acceptable as primary over pressure protection on where applicable bolters, pressure vessels, piping and fusible plugs H Pressure retaining components that do not fall into one of the above categories N Nuclear components: Class 1 □ Class 2 □ Class 3 □, (Meeting AECB or ASME requirements) SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT TYPE OF CONSTRUCTION FORGED O WELDED X WRDUGHT X CAST DOTHE DESCRIBE OTHER LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED: ISO 9001:2015 Certificate, Swagelok Hose Catalog (MS-01-180 rev N) covering FX series, Attachment A, Attachment B, and other supporting documents DECLARATION: tees note at employed by_ Swagelok Company and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by RSI as being suitable for that purpose and I make this solemn declaration conscientiously believing. It to be type, and knowing that it is of the same force and effect as if made under outh. Signature of Declarer. Declared before me at USETHIS SPACE FOR THE This 1350 day of November Jamie L. Ristan OFFICIAL SEAL Resident Portage Count Commissioner of Oaths Notary Public, State of Obio Commission Expires 03/06/2019 or Notary Public: (sign) (Affer Official seal to the right) This space for Regulatory Authority use This registration must be revalidated after ten (10) years from the date of acceptance of and Nunatul OD20522.5 President vessels Act CRN:

1214 FID#: 1. All fittings shall be registered in the name of the Manufacturer. 2. Each category shall be supported with two Statutory Declaration

forms and one copy of supporting documentation. 3. The declaration shall be made by the person having full authority and

responsibility for the quality of the end product.

4. Quality control programs shall be resubmitted for validation

at a maximum interval of five (5) years.

REGISTERED

OD20522.5N

Signed

Chief Inspector

Territorial Registration Fee



Canadian Registration Number Submittal Swagelok Submission # FX-HOSE-2017

May 03, 2018 Page 1 of 5

Attachment B: Scope of Registration for Swagelok FX Series Hose Assemblies (Category D)

Product Scope

The table below represents the scope of Swagelok FX series hose assemblies covered by this submission for CRN approval. These hose assemblies have been evaluated in accordance with ASME B31.3 and ISO 10380. The referenced product catalogues do not represent the full scope of the submission but rather detail some of the most common options.

Summary Table

Product Series	Pressure Retaining Material	End Connection & Sizes	Nom. Hose	Pres	n Working ssure Psig)	Design Code of
			Size (in.)	@ Min. Temp.	@ Max. Temp.	Construction
FX Series Metal Hose	Core: 316L SS (ASTM A240) Braid: 321 SS (ASTM A478) Or 316L SS (ASTM A240) Weld Collar: 304 SS (ASTM A269) End Connections: Strain-Hardened 316 SS (ASTM A479)	Tube Fitting 1/4" – 1/2", 4-10 mm [TA, TM, SL, SM]	1/4	6000 @ -325°F	4236 @ 1000°F	ASME B31.3, ISO 10380
		NPT Female 1/8" – 1/4" [PF] NPT Male 1/8" – 1/2" [PM] Female VCO Fitting 1/4" Male ISO/BSP Tapered threads (ISO 7) 1/4" – 1/2" [MT]		6000 @ -60°F	5640 @ 400°F	
		Female ISO/BSP Tapered Threads (ISO 7) 1/4" [FT]			1	
		Male Swivel Nut VCR ¼" [RM] Female VCR Fitting ¼" [RF]		5500 @ -325°F	3883 @ 1000°F	
		Tube Fitting 12mm [TM]		5365 @ -325°F	3787 @ 1000°F	
		NPT Female 3/8" [PF]		5300 @ -60°F	4982 @ 400°F	
		Tube Butt Weld 1/4" [TB]		5100 @ -325°F	3600 @ 1000°F	
		NPT Female ½" [PF]		4900 @ -60°F	4606 @ 400°F	
		Tube Butt Weld ½" [TB]		3700 @ -325°F	2612 @ 1000°F	
		Male Swivel Nut VCR 1/2" [RM] Female VCR Fitting 1/2" [RF]		3000 @ -325°F	2118 @ 1000°F	





Canadian Registration Number Submittal Swagelok Submission # FX-HOSE-2017

May 03, 2018 Page 2 of 5

Product Series	Pressure Retaining Material	End Connection & Sizes	Nom. Hose	Maximum Working Pressure in (Psig)		Design Code of
			Size (in.)	@ Min. Temp.	@ Max. Temp.	Construction
	Core: 316L SS (ASTM A240) Braid: 321 SS (ASTM A478) or 316L SS (ASTM A240) Weld Collar: 304 SS (ASTM A269) End Connections: Strain-Hardened 316 SS (ASTM A479)	Tube Fitting 1/4" – 1/2", 4-12 mm [TA, TM, SL, SM] Female VCO Fitting 1/2" [VF] Male Swivel Nut VCR 1/4" [RM] Female VCR Fitting 1/4" [RF]	3/8	5000 @ -325°F	3530 @ 1000°F	ASME B31.3, ISO 10380
		NPT Female 1/4" – 1/4" [PF] NPT Male 1/4" – 1/2" [PM] Male ISO/BSP Tapered threads (ISO 7) 1/4" – 3/8" [MT]		5000 @ -60°F	4700 @ 400°F	
		NPT Female ½" [PF]		4900 @ -60°F	4606 @ 400°F	
FX Series Metal Hose		Tube Butt Weld 1/2" [TB]		3700 @ -325°F	2612 @ 1000°F	
		Tube Butt Weld 3/8" [TB]		3300 @ -325°F	2329	
		Male Swivel Nut VCR 1/2" [RM] Female VCR Fitting 1/2" [RF]		3000 @ -325°F	2118 @ 1000°F	
		Tube Fitting 1/4" – 3/4", 6-18 mm [TA, TM, SL, SM] Male Swivel Nut VCR 1/4" [RM] Female VCR Fitting 1/4" [RF] Female VCO Fitting 1/2" [VF]		4500 @ -325°F	3177 @ 1000°F	
		NPT Female 3/8-1/2" [PF] NPT Male 1/4" – 3/4" [PM] Female VCO Fitting 1/4" Male ISO/BSP Tapered threads (ISO 7) 3/8" – 1/2" [MT] Female ISO/BSP Tapered Threads (ISO 7) 1/2" [FT]	1/2	4500 @ -60°F	4230 @ 400°F	
		NPT Female 1" [PF]		4400 @ -60°F	4092 @ 400°F	
		Tube Butt Weld ½" [TB]		3700 @ -325°F	2612 @ 1000°F	
		Male Swivel Nut VCR 1/2" [RM] Female VCR Fitting 1/2" [RF]		3000 @ -325°F	2118 @ 1000°F	
		Male Swivel Nut VCR 3/4" [RM] Female VCR Fitting 3/4" [RF]	UIG	2800 @ -325°F	1976 @ 1000°F	


CRN OD20522.5
Technical Streducts & Salety Authority
Bollogs & Free Surve Vessiols



Canadian Registration Number Submittal Swagelok Submission # FX-HOSE-2017

May 03, 2018 Page 3 of 5

Product Series	Pressure Retaining	End Connection & Sizes	Nom. Hose Size	Maximum Working Pressure in (Psig)		Design Code of
	Material		(in.)	@ Min. Temp.	@ Max. Temp.	Construction
FX Series Metal Hose	Core: 316L SS (ASTM A240) Braid: 321 SS (ASTM A478) Or 316L SS (ASTM A240) Weld Collar: 304 SS (ASTM A269) End Connections: Strain-Hardened 316 SS (ASTM A479)	Tube Fitting 1/2" – 1", 12-20 mm [TA, TM, SL, SM] Female VCO Fitting 1/2" – 3/4" [VF]	3/4	3600 @ -325°F	2541 @ 1000°F	
		NPT Female 1/2"-3/4" [PF] NPT Male 1/2" – 1" [PM] Female VCO Fitting 1/4" Male ISO/BSP Tapered threads (ISO 7) 1/2"-1" [MT] Female ISO/BSP Tapered Threads (ISO 7) 3/4"-1" [FT]		3600 @ -60°F	3384 @ 400°F	
		Male Swivel Nut VCR 1/2" [RM] Female VCR Fitting 1/2"-1" [RF]		3000 @ -325°F	2118 @ 1000°F	
		Male Swivel Nut VCR 5/8"-3/4" [RM] Female VCR Fitting 3/4" [RF]		2800 @ -325°F	1976 @ 1000°F	
		Tube Butt Weld 3/4"-1" [TB]		2400 @ -325°F	1694 @ 1000°F	
		Tube Fitting 1/2" – 1-1/4", 16-28 mm [TA, TM, SL, SM] Male Swivel Nut VCR 1" [RM] Female VCR Fitting 1" [RF] Female VCO Fitting 1" [VF]	1	3000 @ -325°F	2118 @ 1000°F	
		NPT Female 1" [PF] NPT Male 1/2" – 1" [PM] Female VCO Fitting 1/4" Male ISO/BSP Tapered threads (ISO 7) 1" [MT] Female ISO/BSP Tapered Threads (ISO 7) 1" [FT]		3000 @ -60°F	2820 @ 400°F	
		Male Swivel Nut VCR 3/4" [RM] Female VCR Fitting 3/4" [RF]		2800 @ -325°F	1976 @ 1000°F	
		Tube Butt Weld 3/4"-1" [TB]		2400 @ -325°F	1694 @ 1000°F	






Canadian Registration Number Submittal Swagelok Submission # FX-HOSE-2017

May 03, 2018 Page 4 of 5

Product Series	Pressure Retaining Material	End Connection & Sizes	Nominal Hose Size	Maximum Working Pressure in (Psig)		Design Code of
			(in.)	@ Min. Temp.	@ Max. Temp.	Construction
FX Series Metal Hose	Core: 316L SS (ASTM A240) Braid: 321 SS (ASTM A478) or 316L SS (ASTM A240) Weld Collar: 304 SS (ASTM A269) End Connections: Strain-Hardened 316 SS (ASTM A479)	Tube Fitting 1-1/4" – 1-1/2", 28- 32 mm [TA, TM, SL, SM]	1-1/4	2600 @ -325°F	1835 @ 1000°F	ASME B31.3, ISO 10380
		NPT Female 1-1/4" [PF] NPT Male 1" - 1-1/4" [PM] Male ISO/BSP Tapered threads (ISO 7) 1-1/4" [MT]		2600 @ -60°F	2444 @ 400°F	
		Tube Butt Weld 1-1/4" [TB]		2400 @ -325°F	1694 @ 1000°F	
		Tube Fitting 1-1/2", 38 mm [TA, TM, SL, SM] Tube Butt Weld 1-1/2" [TB]	1-1/2	2200 @ -325°F	1553	
		NPT Female 1-1/2" [PF] NPT Male 1" – 1-1/2" [PM] Male ISO/BSP Tapered threads (ISO 7) 1-1/2" - 2" [MT]		2200 @ -60°F	2068 @ 400°F	
		Tube Fitting 2" [TA, SL] Tube Butt Weld 2" [TB]	2	1675 @ -325°F	1182 @ 1000°F	
		NPT Male 1-1/2" – 2" [PM] Male ISO/BSP Tapered threads (ISO 7) 2" [MT]		1675 @ -60°F	1574 @ 400°F	

Product Illustration

All end connections are welded onto the hose using weld collars.





Canadian Registration Number Submittal Swagelok Submission # FX-HOSE-2017 May 03, 2018 Page 5 of 5

Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available within the scope of this approval. Examples of these would include the following:

Braid Options

316L SS

Cover Options

- Armor guard Interlocking, flexible 302 stainless steel.
- Fire jacket Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Thermosleeve Braided fiberglass with saturated synthetic material coating.

Tag and Marking Options

- · Mat tag Polyester tag with customer-specified text
- Lanyard tag Stainless steel tag with customer-specified text
- · Clamp tag Stainless steel tag with customer-specified text

End Connection Seals or Sealant Options

- VCO O-rings
- VCR Gasket
- · Pipe Thread ends thread sealant

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate. The Swagelok FX series hose assemblies are manufactured at Hose Master and at Swagelok Company location in Solon, Ohio.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options.

Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180

