

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
NUNAVUT

NOVA SCOTIA
YUKON

PRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: <u>Swagelok Company</u>	
MANUFACTURERS ADDRESS: <u>29500 Solon Road, Solon, Ohio 44139 USA</u>	
PLANT LOCATIONS: <u>Headquarters: 29500 Solon Road, Solon, Ohio 44139 USA (See Attachment A)</u>	
CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY	
<p>A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers</p> <p>B Flanges: all flanges</p> <p>C Valves: all line valves</p> <p>D Expansion joints, flexible connections, and hose assemblies: all types</p> <p><input checked="" type="radio"/> E Strainers, filters, separators, and steam traps</p> <p>F Measuring devices, including pressure gauges, level gauges, sight glasses, levelts, or pressure transmitters</p> <p>G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs</p> <p>H Pressure retaining components that do not fall into one of the above categories</p> <p>N Nuclear components: Class 1 <input type="checkbox"/> Class 2 <input type="checkbox"/> Class 3 <input type="checkbox"/>. (Meeting AECB or ASME requirements)</p>	TITLE OF THE STANDARD OF CONSTRUCTION ASME B31.1 for unlisted components, ASME B31.3 for unlisted components
SHOW MANUFACTURERS NAME, TRADEMARK OR LOGO AS IT WILL APPEAR ON THE PRODUCT	
<h1>Swagelok</h1>	
TYPE OF CONSTRUCTION FORGED <input type="checkbox"/> WELDED <input type="checkbox"/> WROUGHT <input checked="" type="checkbox"/> CAST <input type="checkbox"/> OTHER <input type="checkbox"/> DESCRIBE OTHER:	
LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED: ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents	

DECLARATION:

I, Joel Feldman, Vice President, Engineering (name and title) employed by Swagelok Company and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by BSI as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: [Signature]

Declared before me at Solon, Ohio

This 14th day of February AD 2019

Commissioner of Oaths
or Notary Public (sign) [Signature]

USE THIS SPACE
OFFICIAL
Notary Public, State of Ohio
Commission Expires: 03/08/2018



This space for Regulatory Authority use
This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: OE21343.5

FID#: 1214

CRN EXPIRES 5 APRIL 29, 2029 - D6


Notes:
1. All fittings shall be registered in the name of the Manufacturer.
2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.

BOILER & PRESSURE VESSEL
NOVA SCOTIA
Data June 7/19
C.R.N. OE21343.58
Dwg. as described
Signed Yvonne Perry
1 of 1
Part
ACT & REGULATIONS


Attachment B: Scope of CRN Registration for Swagelok F, TF, FW and FC Series Filters (Category E)

This document represents the scope of the F, TF, FW and FC Series Filters covered by this submission for CRN approval. These filters were designed and evaluated in accordance with ASME B31.1-2016 for unlisted components and ASME B31.3-2016 for unlisted components.

Summary Table

Product Series	Main Pressure Bearing Component	Main Pressure Bearing Material	Port Connections and Sizes	Maximum Rated Pressure (psig)		Design Code of Construction
				@ 100°F	@ Max Temp.	
2F, 4F	Body	316 SS (ASTM A479)	Tube Fitting 1/8", 1/4", 3mm, 6mm Female NPT 1/8", 1/4" Male NPT 1/4" Male VCR 1/4"	3000	1640 @ 900°F	 ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
6F, 8F	Body	316 SS (ASTM A479)	Tube Fitting 3/8", 1/2"	2500	1360 @ 900°F	
2F, 4F, 6F, 8F	Body	C36000 Brass (ASTM B16)	Tube Fitting 1/8", 1/4", 3/8", 1/2", 6mm, 8mm, 10mm, 12mm Female NPT 1/8", 1/4" Male NPT 1/4", 3/8", 1/2"	1000	680 @ 300°F	
2TF, 4TF, 6TF, 8TF	Body	316 SS (ASTM A479)	Tube Fitting 1/8", 1/4", 3/8", 1/2", 6mm, 8mm, 10mm, 12mm Female NPT 1/8", 1/4" Male NPT 1/4", 3/8", 1/2" Tube Socket Weld 1/4", 3/8"	6000	3280 @ 900°F	
2TF, 4TF, 6TF, 8TF	Body	C36000 Brass (ASTM B16)	Tube Fitting 1/8", 1/4", 6mm, 8mm, 10mm Female NPT 1/8", 1/4" Male NPT 1/4", 3/8", 1/2"	2000	1470 @ 300°F	
			Tube Fitting 3/8"	2000	1430 @ 300°F	
			Tube Fitting 1/2"	2000	1365 @ 300°F	
			Tube Fitting 12mm	2000	1320 @ 300°F	
4TF, 8TF	Body	Alloy 400 N04400 (ASTM B164)	Tube Fitting 1/8", 1/4", 3/8", 6mm, 8mm, 10mm Female NPT 1/8", 1/4" Male NPT 1/4", 3/8", 1/2"	5000	4160 @ 300°F	
			Tube Fitting 1/2"	4400	3652 @ 300°F	
			Tube Fitting 12MM	4208	3493 @ 300°F	
FW	Body	316 SS (ASTM A479)	Tube Fitting 1/4", 6mm Female NPT 1/8", 1/4" Male NPT 1/4" Male VCR 1/4"	6000	3280 @ 900°F	
FC	Body	316 SS (ASTM A479)	Tube Fitting, Female 1/4", 6mm Female NPT 1/8", 1/4" Female ISO 1/4"	1000	760 @ 400°F	

Product Illustration



Typical Product Characteristics

Some product options could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. An example of this would be optional body seal materials.

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. An example of this would be optional filter elements.

All of the above options, those that affect pressure and/or temperature ratings and those that do not, are within the scope of this approval.


Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The below product catalogs do not represent the full scope of registration, but rather details some of the most common options:

- F, TF, FW Series Filter Catalog MS-01-092, Rev L
- FC Series Filter Catalog MS-02-082, R6



Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (Highland) 318 Bishop Road Highland Heights, Ohio 44143 USA	Swagelok Company (Falon 2) 358 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (OFC) 29495 F.A. Lennon Drive Solon, Ohio 44139 USA	Swagelok Company (HPF) 6050 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Atlantic) 26651 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Snow Metal) 6060 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC) 29900 Solon Industrial Parkway Solon, Ohio 44139	Swagelok Company (Strongsville) 15400 Foltz Road Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man

