03-18-2016

UNIFO	RM STATUTORY DECLARA	<u>TION FORM FOR THE REGISTRATIO</u>	N OF FITTING DESIGNS
NEW BRUNSWICK NUNAVUT	NOVA SCOTIA YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NEWFOUNDLAND AND LABRADOR
MANUFACTURERS	NAME: Swagelok Company		
MANUFACTURERS		d, Solon, Ohio 44139-3492	
PLANT LOCATION	S: Headquarters: 29500 Solo	n Road, Solon, Ohio 44139-3492 (See	All I
CATEGO	RY OF FITTINGS TO BE REGISTED	IEO. CIRCLE ONE CATEGORY DNLY	
A Pipe fittings, Incil B Flanges: sil flan C Vaives: all fine v D Expansion joints E Strainers, fillers, F Measuring device pressure trensmi C Certified capacit bollers, pressure	uding couplings, toos, albows, Ya, pit ges raives , flexible connections, and hose asse aoparators, and steam trapa as, including pressure gauges, level p Klers	igs, unions, pipa cape, or reducers mbiles: all types tauges, sight glasses, tevels, or table as primary over pressure protection on	ASME B3 I.3 Chapter IX, for unlisted components where applicable
N Nuclear compon	ents: Clasa 1 🖂 Class 2 🗀 Class 2	D, (Moeling AECB or ASME requirements)	į.
SHOW MANUFACT	URERS NAME, TRADEMARK, OR	LOGO AS IT WILL APPEAR ON THE PRODUC	TYPE OF CONSTRUCTION
S	wagelok	,	FORGED WELDED WROUGHT ST CAST O'THER DESCRIBE OTHER;
LIST OF SUPPOR	TING DOCUMENTATION AND IDEN	ITIFICATION OF THE ACTUAL ITEMS TO BE	OCCUPANT.
tems to be keg	ttachment B, Support Documents Istered: Swagelok IPT Series Valv	, Catalog Information, ISO 9001:2008 Qua es	lity System Certificate
lemperature rating manufacture of in pair alle has declaration conscious at the second conscious at th	oresents the product for which regs, and identification markings are given in the British State of the British Sta	gletration le sought. The dimensions, mate in accordance with the herein named state in accordance with the same force and knowling that it is of the same force and knowling that it is of the same force and herein that it is of the same for	indards. I further declare that the in plant where fabrication occurs in whole
: ان	This registration must be	rovalidated after len (10) years from the	shord Edge Hanga
		10, 10, 10, 10, 10, 10, 10, 10, 10, 10,	A STATE OF THE PARTY OF THE PAR

CRN: <u>0C1B171.5</u> FID#: Notes:

1. All fillings shall be registered in the name of the Manufacturer.

2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.

3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.

4. Quality control programs shall be resubmitted for validation. at a maximum interval of five (5) years.

Attachment B1: Scope of CRN Registration for Swagelok IPT Series Check Valves (Category C)

This document represents the scope of the Swagelok IPT Series Check Valve covered by this submission for CRN approval. The Swagelok IPT Series Check Valves were designed and evaluated in accordance with ASME B31.3 Chapter IX, for unlisted components where applicable.

Summary Table

Description Bea	Main Pressure	essure Bearing Material	Port Connections and Sizes	Maximum Rated Pressure		Design Code
	Bearing Component			At ambient temperature	At maximum temperature	of Construction
CV (soft seat)	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	14,700 @ 250F	ASME B31.3 Chapter IX (For Unlisted Components Where Applicable)
CV (dual seat)	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	14,700 @ 250F	
CV (ball seat)	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	13,900 @ 650F	
CV (soft seat)	Body	ASTM A479	Female NPT 3/4", 1"	10,000 @ 100F	9,800 @ 250F	
CV (dual seat)	Body	ASTM A479	Female NPT 3/4", 1"	10,000 @ 100F	9,800 @ 250F	
CV (ball seat)	Body	ASTM A479	Female NPT 3/4", 1"	10,000 @ 100F	9,300 @ 650F	
CV (soft seat)	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16", 3/4", 1"	20,000 @ 100F	19,600 @ 250F	
CV (dual seat)	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16", 3/4", 1"	20,000 @ 100F	19,200 @ 250F	
CV (ball seat)	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16", 3/4", 1"	20,000 @ 100F	18,600 @ 650F	

Product Illustration



Typical Product Characteristics

Some product options could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. An example of this would be optional body seal materials.

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. An example of this would be different poppet springs.

Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2008. In support of this, Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729 and HSB Registration Services Certificate of Registration Number HQ-Q-4, which apply to all locations listed on the certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

Medium and High Pressure Valves, Fittings and Tubing Catalog MS-02-472




Attachment B2: Scope of CRN Registration for Swagelok IPT Series Double Block and Bleed Valves (Category C)

This document represents the scope of the Swagelok IPT Series Double Block and Bleed Valve covered by this submission for CRN approval. The Swagelok IPT Series Double Block and Bleed Valves were designed and evaluated in accordance with ASME B31.3 Chapter IX, for unlisted components where applicable.

Summary Table

Product Description or Series	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections and Sizes	Maximum Rated Pressure		
				At ambient temperatur e	At maximum temperatur e	Design Code of Construction
DB (ball-needle-ball)	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	14,700 @ 250F	ASME B31.3 Chapter IX (For Unlisted Components Where Applicable)
DB (needle-needle- needle)	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	14,700 @ 250F	
DB (ball-needle-ball)	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16"	15,000 @ 100F	14,700 @ 250F	
DB (needle-needle- needle)	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16"	20,000 @ 100F	19,600 @ 250F	

Product Illustration



Typical Product Characteristics

Some product options could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. An example of this would be optional body seal materials.

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. An example of this would be different handles.

Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2008. In support of this, Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729 and HSB Registration Services Certificate of Registration Number HQ-Q-4, which apply to all locations listed on the certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

Medium and High Pressure Valves, Fittings and Tubing Catalog MS-02-249



Attachment B3: Scope of CRN Registration for Swagelok IPT Series Needle Valves (Category C)

This document represents the scope of the Swagelok IPT Series Needle Valve covered by this submission for CRN approval. The Swagelok IPT Series Needle Valves were designed and evaluated in accordance with ASME B31.3 Chapter IX, for unlisted components where applicable.

Summary Table

Product Pressure Bearing Component		Main Pressure Bearing		Maximum Rated Pressure		Design Code of Construction
	Material (Standard)	Port Connections and Sizes	At ambient temperature	At maximum temperature		
NVT	Body	ASTM A479	Female NPT 1/4", 3/8", 1/2"	15,000 @ 100F	14,700 @ 250F	ASME B31.3 Chapter IX (For Unlisted Components Where Applicable)
NVT	Body	ASTM A479	Female NPT 3/4", 1"	10,000 @ 100F	9,800 @ 250F	
NVT	Body	ASTM A479	Cone-and-Thread (medium) 1/4", 3/8", 9/16"	30,000 @ 100F	29,400 @ 250F	

Product Illustration





Typical Product Characteristics

Some product options could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. An example of this would be optional body seal materials.

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. An example of this would be different handles.

Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2008. In support of this, Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729 and HSB Registration Services Certificate of Registration Number HQ-Q-4, which apply to all locations listed on the certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

Medium and High Pressure Valves, Fittings and Tubing Catalog MS-02-249

