REGISTERED



CRN: CSA-0E21343.56

Technical

Technical
Safety Authority gistration Process administered by 157-9273 Toll Free: (866)530-8599
of Saskatchewarts Group per CSA B51

Email: bollepermits @lsask.ca
Website: www,tsask,ca

2202 2nd Ave.

Statutory Declaration (Registration of Fittings)

		TSK-1008					
l. I	Declaration Information						
I,	Joel Feldman	In this space, show facsimile of					
	Vice President, Engineering	manufacturer's logo or trademark as it will appear on the fitting.					
	(company title, e.g. vice president, plant manager, chief engineer) (must be in a position of authority in the manufacturing plant where the fitting is produced)	2 2					
of:	Swagelok Company	Madelok					
01.	(name of manufacturer)						
loca	ated at: Headquarters: 29500 Solon Road Solon, Ohio	44139 USA					
do s Ves	(Plant Address – Apt/Street) (City.Prov) solemnly declare that the fittings listed hereinunder, which are subject to the Saskissel Safety Act (check one)	(Postal Code) atchewan Boiler and Pressure					
•	WILL	h specifies the dimensions.					
	(title of recognized North American Standard) Materials of construction, pressure / temperature ratings and identification mark	2					
C							
	A	as supported by the attached					
	data which identifies the dimensions, materials of construction, pressure / temp						
	for such ratings, and the marking of the fittings for identification.	•					
veri		g suitable for the manufacturer					
	nese fittings to the stated standard. The fittings covered by this declaration, for whegory E. Filters	ich I seek registration, are					
_							
	upport of this application, the following information, calculations and / or test data a						
Do	9001:2015 Certificate, Attachment A, Attachment B, Catalog Inform	nation and other Support					
II. I	Declaration						
DEC	CLARED before me at In the the	of DNIO					
this	Lith day of February, 2019	The second secon					
Jame L. Ristau Jame L. Ristau Int Portage County							
(p	thic, State of Unio						
(S	gnature of Commissioner of Oaths)						
111.0	Office Use Only						
To th	e best of my knowledge and belief, the application meets the requirements of the Boiler ar	nd Pressure Vessel Safety Act and					
CSA	B51, Clause 4.2, and is accepted for registration in Category						
(R	egistration Number) (Date Registered MM DD YYY)	(Expiry Date – MM DD YYYY)					
	(For the Administrator Chief Inspector)	ABANWATT					
	Group						

Canadian Registration Number Submittal #F-FILTER-2019

Category C: Swagelok Filters

Date: February 4, 2019 Page 1 of 3

Attachment B: Scope of CRN Registration for Swagelok F, TF, FW and FC Series Filters (Category E)

This document represents the scope of the F, TF, FW and FC Series Filters covered by this submission for CRN approval. These files were designed and evaluated in accordance with ASME B31.1-2016 for unlisted components and ASME BY 3-2076 for unlisted components.

Summa	r <u>y Table</u>		Signed Wolfswell			
Product Series	Main Pressure Bearing Component	Main Pressure Bearing Material	178 Rextale Bodlevard, Teroisto, GN Canada (M9W IR Port Connections and Sizes	l li	m Rated re (psig) @ Max Temp.	Design Code of Construction
2F, 4F	Body	316 SS (ASTM A479)	Tube Fitting 1/8",1/4",3mm, 6mm Female NPT 1/8", 1/4" Male NPT 1/4" Male VCR 1/4"	3000	1640 @ 900°F	ART OF 21343.5
6F, 8F	Body	316 SS (ASTM A479)	Tube Fitting 3/8", 1/2"	2500	1360 @ 900°F	7
2F, 4F, 6F, 8F	Body	C36000 Brass (ASTM B16)	Tube Fitting 1/8",1/4",3/8",1/2", 6mm, 8mm, 10mm, 12mm Female NPT 1/8", 1/4" Male NPT 1/4", 3/8", 1/2"	1000	680 @ 300°F	
2TF, 4TF, 6TF,8TF	Body	316 SS (ASTM A479)	Tube Fitting 1/8",1/4",3/8",1/2", 6mm, 8mm, 10mm, 12mm Female NPT 1/8", 1/4" Male NPT 1/4", 3/8", 1/2" Tube Socket Weld 1/4", 3/8"	6000	3280 @ 900°F	
	Body	C26000 Bross	Tube Fitting 1/8",1/4",6mm,8mm, 10mm Female NPT 1/8", 1/4" Male NPT 1/4", 3/8", 1/2"	2000	1470 @ 3 300°F	ASME B31.1 (Unlisted Components)
2TF, 4TF, 6TF, 8TF			Tube Fitting 3/8"	2000	1430 @ 300°F	and ASME B31.3
,			Tube Fitting 1/2"	2000	1365 @ 300°F	(Unlisted Components)
			Tube Fitting 12mm	2000	1320 @ 300°F	
475.075	Body	Alloy 400 N04400 (ASTM B164)	Tube Fitting 1/8",1/4",3/8",6mm, 8mm,10mm Female NPT 1/8", 1/4" Male NPT 1/4", 3/8", 1/2"	5000	4160 @ 300°F	
4TF, 8TF			Tube Fitting 1/2"	4400	3652 @ 300°F	
l diges			Tube Fitting 12MM	4208	3493 @ 300°F	
FW	Body	316 SS (ASTM A479)	Tube Fitting 1/4", 6mm Female NPT 1/8,1/4" Male NPT 1/4" Male VCR 1/4"	6000	3280 @ 900°F	
FC	Body	/ASTM A470\	Tube Fitting, Female 1/4", 6mm Female NPT 1/8", 1/4" Female ISO 1/4"	1000	760 @ 400°F	

Swagelok

Typical Product Characteristics

Canadian Registration Number Submittal #F-FILTER-2019 Category C: Swagelok Filters

Date: February 4, 2019 Page 2 of 3

Product Illustration TF Series F Series **FW Series FC Series**

Some product options could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. An example of this would be optional body seal materials.

178 Rexiste Boulevard, Torox J., UN Canada MSW 1R3

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. An example of this would be optional filter elements.

All of the above options, those that affect pressure and/or temperature ratings and those that do not, are within the scope of this approval.

Swagelok

Canadian Registration Number Submittal #F-FILTER-2019

Category C: Swagelok Filters

Date: February 4, 2019

Page 3 of 3

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The below product catalogs do not represent the full scope of registration, but rather details some of the most common options:

• F, TF, FW Series Filter Catalog MS-01-092, Rev L

• FC Series Filter Catalog MS-02-082, R6



Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man

0E2/343.5

