

Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below



Registration	of Fittings	
Joel Feldman, Vice President of Engineering		
(Name and Position, e.g. President, Plan	i Manager, Chief Engineer)	
F Swagelok Company (Name of Manufac	turnel	
4.5 0 2000 MED NOC CANN	90367800 880 Mail Colonia China	(440) 240 5070
ocated at 29500 Solon Road, Solon, Ohio 44139 USA	(440) 248-4600 (Telephone No.)	(440) 349-5970 (Fex No.)
do solemnly declare that the fittings listed hereunder, which are sand Pressure Vessels Regulation, comply with all of the require ASME B31.1 for unlisted components, and ASME B31.3 for un	subject to the Technical Standard	is and Safety Act , Boilers
(Title of recognized North Amer which specifies the dimensions, materials of construction, pressure/ter		on the fifteen and non-inco
further declare that the manufacture of these fittings is controlled by a q which has been verified by the following authority. BSI he items covered by this declaration, for which I seek registration, are categor is application, the following information and/or lest data are attached as follow SO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Info	uality system meeting the requirement y A. Fittings	ents of ISO 9001:2015type fittings. In support of
(drawings, calculations, les		nerus
commissioner for Oaths: Brenda Hannel (Printed name) (Signature)	(Signature of	Declared
FOR OFFICE US To the best of my knowledge and belief, the application meets the requirem Technical Standards and Safety Act, Boilers and Pressure Vessels Regions CSA Standard B51 and is accepted for registration in Category	nents of Industrial Boil Boil Boil Boil Boil Boil Boil Boi	ers and sure Vessels ty Program
CRN: 0A 21361.5	REGISTER	ED
Registered by:	CRN: 0A 2136	1.5
Dated: May 1, 2019	Signed:	
NOTE: This registration expires on: May 1, 2029	Date: May 1,2	2019
PV 09553 (06/16) For Scope of Registra	trou see attac	hweets A.



Canadian Registration Number Submittal #QC-2019 Category A: Swagelok Quick Connects

Date March 14, 2019 Page 1 of 4

Attachment B: Scope for Swagelok QC, QF, QM and QTM Series Quick-Connects (Category A)

This document represents the scope of the QC, QF, QM, and QTM Series Quick-Connects covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1-2016 for unlisted components and ASME B31.3-2016 for unlisted components.

OA-2/36/, S

Summary Table

Product Description or Series Main Pressure Bearing Component	Standard)	aterial Port Connections and Sizes	Maximum Rated Pressure		Design Code	
			At -50 to 100°F	At maximum temperature	of Construction	
QC4	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 1/8", 1/4", 6MM Female NPT 1/8", 1/4" Female ISO 1/4" Male NPT 1/8", 1/4" Male ISO 1/4"	3000 psi	500 psi @ 400°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
QC6	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 3/8", 10MM Female NPT 1/4", 3/8" Female ISO 3/8" Male NPT 1/4", 3/8" Male ISO 3/8"	1500 psi	400 psi @ 400°F	
QC8	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 1/2", 12MM Female NPT 1/2" Female ISO 1/2" Male NPT 1/2" Male ISO 1/2"	750 psi	300 psi @ 400°F	
QC4	Body	Brass C36000 (ASTM B16)	Swagelok Tube Fitting 1/8", 1/4", 6MM Female NPT 1/8", 1/4" Female ISO 1/4" Male NPT 1/8", 1/4" Male ISO 1/4"	2000 psi	300 psi @ 250°F	
QC6	Body		Swagelok Tube Fitting 3/8", 10MM Female NPT 1/4", 3/8" Female ISO 1/4", 3/8" Male NPT 1/4", 3/8" Male ISO 1/4", 3/8"	1000 psi	300 psi @ 250°F	
QC8	Body	Brass C36000 (ASTM B16)	Swagelok Tube Fitting 1/2", 12MM Female NPT 1/2" Female ISO 1/2" Male NPT 1/2" Male NPT 1/2"	500 psi	300 psi @ 250°F	



Canadian Registration Number Submittal #QC-2019 Category A: Swagelok Quick Connects

Date March 14, 2019 Page 2 of 4

Progettro	Main Pressure	the later than the same of the	Maximum Rated Temperature		Design Code	
Description or Series	Bearing Component	Bearing Material (Standard)	Port Connections and Sizes	At -50 to 100°F	At maximum temperature	of Construction
QF4, QF8 Body 316 SS (ASTM A479)	Rody	Swagelok Tube Fitting 1/4", 3/8", 1/2", 6MM Female NPT 1/4", Female ISO Tapered 1/4" Female ISO Parallel 1/4"	6000 psi	400 psi @ 400°F	DART	
		Female NPT 3/8"	5300 psi	400 psi @ 400°F	DA 21361.	
		Female NPT 1/2" Female ISO Tapered 1/2" Female ISO Parallel 1/2"	4900 psi	400 psi @ 400°F	tads & Safety Aut Free sure Ves ty Program	
QF12, QF16	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 3/4", 1" Female NPT 3/4", 1"	4000 psi	200 psi @ 400°F	
		Swagelok Tube Fitting 1/4"	3500 psi	300 psi @ 250°F		
			Swagelok Tube Fitting 6MM	3190 psi	300 psi @ 250°F	
QF4 Body C36000 (ASTM B16		Swagelok Tube Fitting 3/8"	2200 psi	300 psi @ 250°F	ASME B31.1 (Unlisted Components and	
		Female NPT 1/4" Female ISO Tapered 1/4" Female ISO Parallel 1/4"	3300 psi	300 psi @ 250°F		
		Female NPT 3/8"	2400 psi	300 psi @ 250°F		
			Swagelok Tube Fitting 3/8"	2200 psi	300 psi @ 250°F	ASME B31.3 (Unlisted Components
QF8 Body C36000 (ASTM B16)	y C36000	Swagelok Tube Fitting 1/2"	2100 psi	300 psi @ 250°F	Components	
		Female NPT 3/8"	2600 psi	300 psi @ 250°F		
	100000000000000000000000000000000000000	Female NPT 1/2" Female ISO Tapered 1/2" Female ISO Parallel 1/2"	2400 psi	300 psi @ 250°F		
QF12, Body C360		Swagelok Tube Fitting 3/4"	1800 psi	200 psi @ 250°F		
	Brass C36000 (ASTM B16)	Swagelok Tube Fitting 1"	1500 psi	200 psi @ 250°F		
	(AOTM 010)	Female NPT 3/4", 1"	2000 psi	200 psi @ 250°F		
QM2	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 1/16", 1/8" Female NPT 1/16", 1/8" Male NPT 1/16", 1/8"	4000 psi	200 psi @ 400°F	
QM2	Body	Brass C36000 (ASTM B16)	Swagelok Tube Fitting 1/16",1/8" Female NPT 1/16", 1/8" Male NPT 1/16", 1/8"	2000 psi	200 psi @ 250°F	



Canadian Registration Number Submittal #QC-2019 Category A: Swagelok Quick Connects

Date March 14, 2019 Page 3 of 4

Product Description or Series Main Pressure Bearing Component	Proseuro	Bearing Material Port Connections and Sizes	Post Community and Cine	Maximum Rated Temperature		Design Code of Construction	
	(Standard)		At -50 to 100°F	At maximum temperature			
QTM2	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 1/4", 3/8", 6MM, 8MM Male NPT 1/4", 3/8" Female NPT 1/8",1/4", 3/8" Female ISO Tapered 1/4" Female ISO Parallel 1/8", 1/4"	4500 psi	4500 psi @ 120°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted	
QTM4, QTM8	Body	316 SS (ASTM A479)	Swagelok Tube Fitting 1/4", 3/8", 1/2", 3/4", 1", 6MM, 10MM, 12MM Male NPT 1/4", 3/8", 1/2", 3/4", 1" Female ISO Tapered 1/4", 1/2" Female ISO Parallel 1/4", 1/2" JIC 37° flare 1/4", 1/2"	3200 psi	3200 psi @ 120°F		
QTM2	Body	Alloy 400 (ASTM B164)	Swagelok Tube Fitting 1/4", 3/8", 6MM, 8MM Male NPT 1/4", 3/8" Female NPT 1/8",1/4", 3/8" Female ISO Tapered 1/4" Female ISO Parallel 1/8", 1/4"	3200 psi	3200 psi @ 120°F	Components)	





Canadian Registration Number Submittal #QC-2019 Category A: Swageiok Quick Connects Date March 14, 2019 Fage 4 of 4

Product Options:

Some product options could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. An example of this would be optional body seal materials.

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. An example of this would be optional lubricants.


Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

QC, QF, QM, and QTM Series Quick-Connects Catalog MS-01-138, Rev S



Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man

