



Technical Standards and Safety Authority
 345 Carlingview Drive
 Toronto, Ontario M9W 6N9
 www.tssa.org

Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below



STATUTORY DECLARATION Registration of Fittings

I, Joel Feldman, Vice President of Engineering
(Name and Position, e.g. President, Plant Manager, Chief Engineer)

of Swagelok Company
(Name of Manufacturer)

Located at 29500 Solon Road, Solon, Ohio 44139 USA (440) 248-4600 (440) 349-5970
(Plant Address) (Telephone No.) (Fax No.)

do solemnly declare that the fittings listed hereunder, which are subject to the *Technical Standards and Safety Act*, Boilers and Pressure Vessels Regulation, comply with all of the requirements of ASME B31.1 for unlisted components, and ASME B31.3 for unlisted components
(Title of recognized North American Standard)
 which specifies the dimensions, materials of construction, pressure/temperature ratings, identification marking the fittings and service;

or are not covered by the provisions of a recognized North American standard and are therefore manufactured to comply with as supported by the attached data which identifies the dimensions, material of construction, pressure/temperature ratings and the basis for such ratings, the marking of the fitting for identification and service.

I further declare that the manufacture of these fittings is controlled by a quality system meeting the requirements of ISO 9001:2015 which has been verified by the following authority, BSI

The items covered by this declaration, for which I seek registration, are category C. Valves type fittings. In support of this application, the following information and/or test data are attached as follows:
ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents
(drawings, calculations, test reports, etc.)

Declared before me at _____ in the _____ of _____
 the _____ day of _____ AD 20_____.

Commissioner for Oaths:

Unable to get a notary signature
(Printed name)
or seal due to Covid-19 situation
April 22, 2020
(Date)


(Signature of Declarer)

FOR OFFICE USE ONLY

To the best of my knowledge and belief, the application meets the requirements of the *Technical Standards and Safety Act*, Boilers and Pressure Vessels Regulation, and CSA Standard B51 and is accepted for registration in Category C.

CRN: DC22506.5
 Registered by: 
 Dated: JUNE 17, 2020



This Document has been digitally signed. The stamp size has been optimized for 11 x 17 documents.

| | |
|---|---|
| Technical Standards and Safety Authority | Boilers and Pressure Vessels Safety Program |
| REGISTERED | |
| CRN: DC22506.5 | |
| Signed:  | |
| Date: June 17, 2020. | |

NOTE: This registration expires on: JUNE 17, 2030

FOR SCOPE OF REGISTRATION SEE STAMPED ATTACHMENT A AND B

**Information provided in this application is releasable under the Freedom of Information and Privacy Protection Act and may be disclosed upon request.*



Attachment B: Scope for Swagelok BV Series Bleed Valves and P Series Purge Valves (Category C)

This document represents the scope of the Swagelok BV Bleed Valves and P Purge Valves covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1-2018 for unlisted components and ASME B31.3-2018 for unlisted components.

Summary Table

| Product Series | Main Pressure Bearing Component | Main Pressure Bearing Material (Standard) | Port Connections, Sizes | Maximum Rated Pressure (psig) | | Design Code of Construction |
|----------------|---------------------------------|---|--|--|--------------------|---|
| | | | | At -65 to 100°F (except Carbon Steel) | At max temperature | |
| BV | Body, Stem | 316 SS (ASTM A479) | Male NPT 1/8", 1/4", 3/8", 1/2" | 10,000 | 6085 @ 850°F | ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components) |
| | | | Male ISO 1/4", 1/2" | | | |
| | | | Male SAE 1/4", 1/2" | 4,568 | 4568 @ 400°F | |
| BV | Body, Stem | 1018 Carbon Steel (ASTM A108) | Male NPT 1/8", 1/4", 3/8", 1/2" | 10,000 @ -20 to 100°F | 8630 @ 375°F | |
| | | | Male ISO 1/4", 1/2" | | | |
| | | | Male SAE 1/4", 1/2" | 4,568 @ -20 to 100°F | 4568 @ 375°F | |
| P | Body, Cap | 316 SS (ASTM A479) | Female & Male NPT 1/8", 1/4", 3/8", 1/2" | 4000 | 2500 @ 600°F | |
| | | | Male ISO 1/8" | | | |
| | | | Swagelok Tube Fitting 1/8", 1/4", 3/8", 1/2", 6MM, 8MM | Male SAE 1/4", 1/2" | 4000 | 2850 @ 400°F |
| P | Body, Cap | 12L14 Carbon Steel (ASTM A108) | Female & Male NPT 1/8", 1/4", 3/8", 1/2" | 3000 @ -20 to 100°F | 3000 @ 250°F | |
| | | | Male SAE 1/4", 1/2" | | | |
| | | | Male ISO 1/8" | Swagelok Tube Fitting 1/8", 1/4", 3/8", 1/2", 6MM, 8MM | | |

| Product Series | Main Pressure Bearing Component | Main Pressure Bearing Material (Standard) | Port Connections, Sizes | Maximum Rated Pressure (psig) | | Design Code of Construction | |
|---------------------|---------------------------------|---|---|-------------------------------|--------------------|---|-------------|
| | | | | At -65 to 100° | At max temperature | | |
| P | Body, Cap | Brass C36000 (ASTM B16) | Male NPT 1/8", 1/4", 1/2" | 3000 | 740 @ 400°F | ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components) | |
| | | | Male ISO 1/8" | | | | |
| | | | Swagelok Tube Fitting 1/8", 1/4", 3/8", 1/2", 6MM | 2322 | | | |
| | | | Swagelok Tube Fitting 8MM | | | | |
| | | | Swagelok Tube Fitting 3/8" | 2200 | | | |
| | | | Swagelok Tube Fitting 1/2" | 2100 | | | |
| | | | 1/8" FNPT | 3000 | | | 640 @ 400°F |
| | | | 1/4" FNPT | 3000 | | | 660 @ 400°F |
| | | | 3/8" FNPT | 2600 | | | 520 @ 400°F |
| | | | 1/2" FNPT | 2400 | | | 480 @ 400°F |
| Male SAE 1/4", 1/2" | 2284 | 297 @ 400°F | | | | | |

Product Illustrations

BV Series Bleed Valves



P Series Purge Valves



Typical Product Characteristics:

Some of the product options listed below could affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

BV Series Bleed Valves

- Handles
- Vent Tubes

P Series Purge Valves

- Ball Material (316SS standard, PTFE optional)

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

- BV Bleed Valves and P Purge Valves Catalog MS-01-62, Rev N

THIS IS PART OF CRN
 0C22506.5
 Technical Standards and Safety Authority
 Boilers and Pressure Vessels Safety
 Program

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

| | |
|---|--|
| Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA | Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA |
| Swagelok Company (Highland) 318 Bishop Road Highland Heights, Ohio 44143 USA | Swagelok Company (Falon 2) 358 Bishop Road Highland Heights, Ohio 44143 USA |
| Swagelok Company (OFC) 29495 F.A. Lennon Drive Solon, Ohio 44139 USA | Swagelok Company (HPF) 6050 Cochran Road Solon, Ohio 44139 USA |
| Swagelok Company (Atlantic) 26651 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA | Swagelok Company (Snow Metal) 6060 Cochran Road Solon, Ohio 44139 USA |
| Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA | Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139 |
| Swagelok Hose Services Company (SHSC) 29900 Solon Industrial Parkway Solon, Ohio 44139 | Swagelok Company (Strongsville) 15400 Foltz Road Strongsville, Ohio 44119 |
| Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China | Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man |