UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS NEW BRUNSWICK NOVA SCOTIA PRINCE EDWARD ISLAND NEWFOUNDLAND AND LABRADOR NUNAVUT YUKON NORTHWEST TERRITORIES MANUFACTURERS NAME: Swagelok Company MANUFACTURERS ADDRESS: 29500 Solon Road, Solon, Ohio 44139 USA PLANT LOCATIONS: Headquarters: 29500 Solon Road, Solon, Ohio 44139 USA (See Attachment A) CATEGORY OF FITTINGS TO BE REGISTERED, CIRCLE ONE CATEGORY ONLY THE OF THE STANDARD OF CONSTIBUCTION Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers ASME B31.1 for Flanges: all flanges C Valves: all line valves unlisted components. D Expansion joints, flexible connections, and hose assemblies: all types E Strainers, filters, separators, and steam trape ASME B31.3 for Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or unlisted components pressure transmitters G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on botters, pressure vessets, piping and fusible plugs

H Pressure retaining components that do not fall into one of the above categories N Nuclear components: Class 1 □ Class 2 □ Class 3 □, (Meeting AECB or ASME requirements) SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT TYPE OF CONSTRUCTION FORGED M WELDED O WROUGHT M LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED: ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents [Joel Feldman, Vice President, Engineering (see role 3) employed by_ Swagelok Company and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by BSI as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under path. Signature of Declarer: A CELFOR Declared before me at USE THIS SP OFFICIAL Commissioner of Oaths or Notary Public: (sign) _ ON BYF (Affix Official seal to the right) This space for Regulatory Authority use This registration must be revalidated after ten (10) years from the date of propage. PROVINCE OF PRINCE EDWARD ISLAND COMMUNITIES, LAND & ENVIRONMENT ALLOY C-276 TUSE FITTINGS - UP TO 11,000PM. G

DATE:

INSPECTION SERVICES SECTION

BOILER/PRESSURE VESSEL BRANCH

Notes:


1. All fittings shall be registered in the name of the Manufacturer. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
 The declaration shall be made by the person having full authority and

Quality control programs shall be resubmitted for validation

CPN EXPIRES MARCH 2, 2030-0.6.

responsibility for the quality of the end product.

at a maximum interval of five (5) years.



Revised February 6, 2020 Page 1 of 3

Attachment B. Scope of Registration for Swagelok Alloy C-276 (ASTM B564, B574) Tube Fittings (Category A)

This document represents the scope of Swagelok Alloy C-276 Tube Fittings covered by this submission for CRN approval. These Swagelok Tube Fittings have been evaluated in accordance with ASME B31.3 for unlisted components and ASME B31.1 for unlisted components.

Summary Table

Product Description or Series	Material (Standard)	Port Connections and Sizes	Maximum Allowable Working Pressure		Design Code
			Up to 100°F	At maximum temperature	of Construction
Gaugeable Tube Fittings and Adapter Fittings	Alloy C276 (ASTM B564 / ASTM B574)	Swagelok End Connection 1/4 inch – 1/2 inch 6mm - 12mm	See Table below	See Table below	ASME B31.3 (Unlisted Components) ASME B31.1 (Unlisted Components)
		NPT Male 1/16 - 1 inch	11 000 – 5300 psig	9020 - 4350 psig @ 1000°F (537°C)	
		NPT Female 1/16 - 1 inch	6700 – 4400 psig	5500 - 3610 psig @ 1000°F (537°C)	

Alloy C-276 Swagelok Tube Fitting Pressure Rating Table

STATE OF THE STATE	Maximum Allowable Working Pressure		
Swagelok End Connection Size	Up to 100°F	At maximum temperature 1000°F (537°C)	
1/4 inch	10 200 psig	7752 psig	
3/8 inch	6500 psig	4940 psig	
1/2 inch	5100 psig	3876 psig	
6mm	670 bar	509 bar	
10mm	380 bar	289 bar	
12mm	310 bar	235 bar	



Product Description


Swagelok Fittings are furnished in a variety of configurations and shapes (straight, elbow, tee or cross). Swagelok Fittings consist of at least one Swagelok End – a proprietary two-ferrule mechanical-grip design. The table below, as well as the "Configurations" section, covers a variety of other end connections.






Configurations

1. Unions.



2. Male and Female connectors / adapters.



NPT Male Connectors

Female Connectors



Revised February 6, 2020 Page 3 of 3

Product Options:

Some of the product options listed below affect the pressure-temperature ratings in the "Scope of Registration" section above, but in all cases the pressure ratings are the same or less than those shown in the Summary Table on page 1.

- · Sealant for NPT pipe threads -
 - Curable resin with PTFE
 - o PTFE tape
- Bored through fittings
- Plastic ferrules, (Nylon, Teflon, PEEK)

Additional options that do not affect pressure and/or temperature ratings may be made available within the scope of this approval. Examples of these would include the following:

- Special marking
- Special cleaning
- Wire drills
- bulkhead configurations
- · Snubbers/frits and orifice plates

All of the above options, those that affect pressure and/or temperature ratings and those that do not, are within the scope of this approval.

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options.

- Gaugeable Tube Fittings and Adapter Fittings MS-01-140, Rev Y
- Swagelok Tubing Data Sheet MS-01-107, Rev N



Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)	
29500 Solon Road	348 Bishop Road	
Solon, Ohio 44139	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (Highland)	Swagelok Company (Falon 2)	
318 Bishop Road	358 Bishop Road	
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (OFC)	Swagelok Company (HPF)	
29495 F.A. Lennon Drive	6050 Cochran Road	
Solon, Ohio 44139	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)	
26651 Curtiss Wright Parkway	6060 Cochran Road	
Willoughby Hills, Ohio 44092	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139	
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)	
29900 Solon Industrial Parkway	15400 Foltz Road	
Solon, Ohio 44139	Strongsville, Ohio 44119	
Swagelok (China) Fluid System Technologies Ltd.	Swagelok Company A.G. (European Technology	
Changshu Export Process Zone	Center)	
Changshu Economic Development Zone	St. GallerstraBe 84	
Changshu, Jiangshu	Lachen, Switzerland 8853	
215513 China	Switzerland	
Swagelok Limited Tromode M4 4RA sle of Man		

