DocuSign Envelope ID: 763C8834-FA34-47AD-A1D5-74867869CC6A ORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUNAVUT

NOVA SCOTIA YUKON PRINCE EDWARD ISLAND NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: Swagelok Company	
MANUFACTURERS ADDRESS: 29500 Solon Road, Solon, Ohio 44139 USA	
PLANT LOCATIONS: Headquarters: 29500 Solon Road, Solon, Ohio 44139 USA (See Atta	chment Al
CATEGORY OF FITTINGS TO BE REGISTERED, CIRCLE ONE CATEGORY ONLY	TITLE OF THE STANDARD OF CONSTRUCTION
A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers B Flanges: all flanges O'Valves: all line valves E Expansion joints, flexible connections, and hose assemblies: all types E Strainers, filters, separators, and steam traps F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fuelble pluge	ASME B31.1 for unlisted components, ASME B31.3 for unlisted components
H Pressure retaining components that do not fall into one of the above categories N Nuclear components: Class 1 Class 2 Class 3 . (Meeting AECB or ASME requirements)	
SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT	TYPE OF CONSTRUCTION
Swagelok	FORGED CI WELDED CI WROUGHT CI CAST CI OTHER 10 DESCRIBE OTHER: BSF
LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REG	ISTERED:
DECLARATION:	
I Joel Feldman, Vice President, Engineering (sae note 3) employed by Swagelok Company and bein responsibility for the quality of the end product do solemnly declare that the information contained my knowledge represents the product for which registration is sought. The dimensions, materials temperature ratings, and identification markings are in accordance with the herein named standar manufacture of these fittings is regulated by a Quality Control Program which extends to each plan or in part and has been verified by BSI as being suitable for that declaration conscientiously believing, it to be true, and knowing that it is of the same force and effect of the same force and	of construction, pressure is. I further declare that the at where fabrication occurs in whole
	ct as if made under oath.
Signature of Declarer: Asl () 10/18/2021 8:19 AM EDT	ct as if made under oath.
Signature of Declarer: 10/18/2021 8:19 AM EDT	clasif made under oath.
Signature of Declarer: 10/18/2021 8:19 AM EDT Declared before me at 11/2010 to get a motary USE THIS This day of signature UPSeal dire to OFFI Commissioner of Oaths or Notary Public: (sign) COVID-19 situation (Affix Official seal to the right)	ct as if made under oath.
Signature of Declarer: Declared before me at	ctasifmade under oath. SPACE FOR THE CIAL SEAL
Signature of Declarer: Declared before me at	ctasifmade under oath. SPACE FOR THE CIAL SEAL
Signature of Declarer: Declared before me at Declared before me at Declared to get a notary U.S.E.T.H.I.S.	Ct as if made under cath. SPACE FOR THE CIAL SEAL acceptance. NCEEDWARD ISLAND ND & ENVIRONMENT



Canadian Registration Number Submittal
Category C: Swagelok RHPS Series LRS4 and BS6

Technical Standards and Safety Authority
Date: September 29, 2021
Regulators
Program
Pressure Vessels Safety
Program
Pressure Vessels Safety
Page 1 of 2

THIS IS PART OF CRN

0C23691.5

Program

Page 1 of 2

Attachment B: Scope of CRN for Swagelok BS6 and LRS4 Regulators (Category C)

This document represents the scope of bolted / threaded-body RHPS Series, BS6 and LRS4 Series Pressure Regulators covered by this submission for CRN approval. These spring-loaded regulators have been evaluated in accordance with ASME B31.1-2020 and B31.3-2020 for unlisted components.

Summary Table

#	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections, Sizes	Maximum Rated Pressure				Danium Cada
Product Series				At Ambient temperature		At maximum temperature		Design Code of
				Inlet	Outlet	Inlet	Outlet	Construction
BS6	Body	316L SS UNS 31603 (ASTM A479)	Female NPT, 3/4" in. ASME/ANSI B16.5 Flange (600#, 900#, 1500#, 2500#)	1015 psi (70 bar)	203 psi (14 bar)	1015 psi (70 bar)	203 psi (14 bar)	ASME B31.1/ ASME B31.3 (Unlisted Components)
			ASME/ANSI B16.5 Flange (300#)	600 psi (41 bar)	203 psi (14 bar)	600 psi (41 bar)	203 psi (14 bar)	
			ASME/ANSI B16.5 Flange (150#)	230 psi (16 bar)	203 psi (14 bar)	230 psi (16 bar)	203 psi (14 bar)	
LRS4	Body	316L SS UNS 31603 (ASTM A479	Female NPT, 1/2 in.	507 psi (35 bar)	290 psi (20 bar)	507 psi (35 bar)	290 psi (20 bar)	

Product Illustration



BS6 Series Regulator



LRS4 series Regulator



Canadian Registration Number Submittal
Category C: Swagelok RHPS Series LRS4 and BS6 Regulators

Product Options:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

Seal Materials

Fluorocarbon FKM
Nitrile
EPDM
FFKM
Low temperature Nitrile

Diaphragm Materials

Fluorocarbon FKM
Nitrile
EPDM
FFKM
Low temperature Nitrile
PTFE
316L SS

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

RHPS Regulators Series Catalog MS-02-430, Rev K

THIS IS PART OF CRN

Date: September 29, 2021

Page 2 of 2

0C23691.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

THIS IS PART OF CRN

0C23691.5

Swagelok Company 29500 Solon Road	Technical Standards and Safety Authority Swagelok Company (Palibrins 1a)nd Pressure Vessels Safety 348 Bishop Road Program				
Solon, Ohio 44139	Highland Heights, Ohio 44143				
USA	USA				
Swagelok Company (Highland)	Swagelok Company (Falon 2)				
318 Bishop Road	358 Bishop Road				
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143				
USA	USA				
Swagelok Company (OFC)	Swagelok Company (HPF)				
29495 F.A. Lennon Drive	6050 Cochran Road				
Solon, Ohio 44139	Solon, Ohio 44139				
USA	USA				
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)				
26651 Curtiss Wright Parkway	6060 Cochran Road				
Willoughby Hills, Ohio 44092	Solon, Ohio 44139				
USA	USA				
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139				
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)				
29900 Solon Industrial Parkway	15400 Foltz Road				
Solon, Ohio 44139	Strongsville, Ohio 44119				
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man				