### UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUNAVUT	NOVA SCOTIA YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NEWFOUNDLAND AND LABRADOR
MANUFACTURERS NAME:	Swagelok Company		
MANUFACTURERS ADDRES		i, Solon, Ohio 44139 USA	
PLANT LOCATIONS: Head		Road, Solon, Ohio 44139 USA (See	Attachment A)
CATEGORY OF FO	TINGS TO BE REGISTER	ED. CIRCLE ONE CATEGORY ONLY	TITLE OF THE STANDARD OF CONSTRUCTION
H Flangus: all flanges  (Valves: all fine valves  Expansion joints, flexible of  E Strainers, filters, separator  F Measuring devices, including pressure transmitters  G Certified capacity-rated proboilers, pressure vessels,  H Pressure retaining components	onnections, and hose asset s, and steam traps ng pressure gauges, level g essure relief devices accept piping and fusible pluga tents that do not fall into on	auges, sight glassos, levels, or able as primary over pressure protection on a of the above categories	ASME B31.1 for unlisted components, ASME B31.3 for unlisted components
N Nuclear components: Class	AME TRADEMARK OR	O. (Meeting AECB or ASME requirements) OGO AS IT WILL APPEAR ON THE PRODI	UCT TYPE OF CONSTRUCTION
Swa	delok	OGO AS II. WILL AFFEAR ON THE FROM	FORGED CI WELDED CO WROUGHT M CAST CI OTHER CI DESCRUSE OTHER:
LIST OF SUPPORTING DOG	UMENTATION AND IDEN	TIFICATION OF THE ACTUAL ITEMS TO B	E REGISTERED:
ISO 9001:2015 Certificati	e. Attachment A. Attachn	ent B, Catalog Information and other Su	apport Documents
responsibility for the quality my knowledge represents t temperature ratings, and id manufacture of these fitting or in part and has been year	of the end product do she product for which reg entification markings are is is regulated by a Qualified by BSI believing it to be true, a	elemnly declare that the information con- istration is sought. The dimensions, ma- in accordance with the herein named si ity Control Program which extends to ea- as being suitable in nd knowing that it is of the same force as	landards. I further declare that the chiptant where fabrication occurs in whole for that purpose and I make this solemn and effect as if made under oath.  ISSPACE FOR THE
Commissioner of Oaths		-19 situation - June 5,	
or Notary Public: (sign)			may very shift, feet o
	(Affix Official seel to the		
CRN: 0C22514.5	T	his space for Regulatory Authority use evalidated after ten (10) years from the o	
FIDS: 1214 31, S, M, L series Notes: locations. 1. All fillings shall be registe	red in the name of the Man	14 plant PROVINCE OF PR COMMUNITIES, I	CEPTED INCE EDWARD ISLAND AND & ENVIRONMENT 225/459
Each category shall be so forms and one copy of supports.     The declaration shall be responsibility for the quality 4. Quality control programs.	orting documentation. nade by the person having of the end product.	full authority and	SERVICES SECTION
at a maximum interval of five CRN expires June	22, 2030 - DG	BOILER/PRESS	URE VESSEL BRANCH



THIS IS PART OF CRN
0C22514.5
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Date: June 5, 2020 Page 1 of 2

# Attachment B: Scope for Swagelok 31, S, M, and L Series Metering Valves (Category C)

This document represents the scope of the Swagelok 31, S, M, and L Series Metering Valves covered by this submission for CRN approval. These products were designed and evaluated in accordance with ASME B31.1-2018 for unlisted components and ASME B31.3-2018 for unlisted components.

#### **Summary Table**

Product	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections, Sizes	Maximum Rated Pressure (psig)		Design Code
Series				At -10 to 100°F (except 31 Series)	At max temperature	of Construction
31	Body, Bonnet	316 SS (ASTM A479)	Tube Fitting 1/4",6MM Female NPT 1/8",1/4"	5000 @ -65 to 100°F	3435 @ 450°F 2815 @ 850°F	
S	Body, Bonnet	316 SS (ASTM A479)	Tube Fitting 1/16", 1/8",1/4", 3MM,6MM Male VCR 1/4"	2000	2000 @ 400°F	ASME B31.1 (Unlisted
M	Body, Bonnet	316 SS (ASTM A479)	Tube Fitting 1/8", 1/4", 3MM, 6MM Male NPT 1/8", 1/4" Female NPT 1/8" Male VCR 1/4"	1000	1000 @ 400°F	Components) and ASME B31.3 (Unlisted Components)
L	Body, Bonnet	316 SS (ASTM A479)	Tube Fitting 1/4", 3/8", 6MM Male NPT 1/4"	1000	1000 @ 400°F	
S	Body, Bonnet	Brass C37700 (ASTM B283)	Tube Fitting 1/16", 1/8",1/4", 3MM,6MM	2000	2000 @ 200°F	
М	Body, Bonnet	Brass C37700 (ASTM B283)	Tube Fitting 1/8", 1/4", 3MM, 6MM Male NPT 1/8", 1/4" Female NPT 1/8"	1000	1000 @ 200°F	ASME B31.1 (Unlisted Components)
L	Body, Bonnet	Brass C37700 (ASTM B283)	Tube Fitting 1/4", 3/8", 6MM Male NPT 1/4"	1000	1000 @ 200°F	
S Body Bonne	Body,		Tube Fitting 1/16", 1/8", 1/4", 6MM	2000	2000 @ 300°F	
	Donnet		Tube Fitting 3MM	2000	1885 @ 300°F	
М	Body, Bonnet	Brass C37700 (ASTM B283)	Tube Fitting 1/8", 1/4", 3MM, 6MM Male NPT 1/8", 1/4" Female NPT 1/8"	1000	1000 @ 300°F	ASME B31.3 (Unlisted Components)
L	Body, Bonnet	Brass C37700 (ASTM B283)	Tube Fitting 1/4", 3/8", 6MM Male NPT 1/4"	1000	1000 @ 300°F	



Canadian Registration Number Submittal Category C: Swagelok Metering Valves

#### **Product Illustration**



Date: June 5, 2020

Page 2 of 2

#### **Typical Product Characteristics**

Additional options that do not affect pressure-temperature ratings may be made available within the scope of this registration. Examples of these would include stem seal materials and handles.

#### **Quality System**

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

#### References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

31, S, M, L Series Metering Valves Catalog MS-01-142, R11

## **Attachment A. Swagelok Manufacturing Locations**

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA  THIS IS PART 0C22514.5 Technical Standards and	Safety Authority
Swagelok Company (Highland) 318 Bishop Road Highland Heights, Ohio 44143 USA	Swagelok Company (Falon 2) 358 Bishop Road Highland Heights, Ohio 44143 USA  Boilers and Pressure V Program	essels Safety
Swagelok Company (OFC) 29495 F.A. Lennon Drive Solon, Ohio 44139 USA	Swagelok Company (HPF) 6050 Cochran Road Solon, Ohio 44139 USA	
Swagelok Company (Atlantic) 26651 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Snow Metal) 6060 Cochran Road Solon, Ohio 44139 USA	
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139	
Swagelok Hose Services Company (SHSC) 29900 Solon Industrial Parkway Solon, Ohio 44139	Swagelok Company (Strongsville) 15400 Foltz Road Strongsville, Ohio 44119	
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man	