UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NOVA SCOTIA PRINCE EDWARD ISLAND NEWFOUNDLAND AND LABRADOR NUNAVUT YUKON NORTHWEST TERRITORIES MANUFACTURERS NAME: Swagelok Company MANUFACTURERS ADDRESS: 29500 Solon Road, Solon, Ohio 44139 USA PLANT LOCATIONS: Headquarters: 29500 Solon Road, Solon, Ohio 44139 USA (See Attachment A) CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY TITLE OF THE STANDARD OF CONSTRUCTION A Pipe fittings, including couplings, tees, elbows, Ye, plugs, unions, pipe caps, or reducers ASME B31.1 for B Flanges: all flanges Ovalves: all line valves unlisted components, D Expansion joints, flexible connections, and hose assemblies: all types ASME B31.3 for E Strainers, filters, separators, and steam traps unlisted components F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs H Pressure retaining components that do not fall into one of the above categories N Nuclear-components: Class 1 ☐ Class 2 ☐ Class 3 ☐, (Meeting AECB or ASME requirements) SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT TYPE OF CONSTRUCTION FORGED [] WELCED [] WROUGHT () LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED: ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents DECLARATION: [Joel Feldman, Vice President, Engineering [300 note 3] employed by Swagelok Company and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of and being the person having full authority and my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by BSI as being suitable for that purpose and I make this solemn decisration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath. C. Fell Signature of Declarer: Declared before me at Unable to get a notary signature THIS SPACE FOR THE day of or seal due to COVID-19 OFFICIAL SEAL Commissioner of Oaths or Notery Public: (sign) situation - August 27, 2020 (Affix Official seal to the right) This space for Regulatory Authority use This registration must be revalidated after ten (10) years from the date of acceptance. CRN: 0C22706.5 ACCEPTED PROVINCE OF PRINCE EDWARD ISLAND 1214 FID#: Sno-Trik 410 (B31.1, B31.3), 445, 645 and 945 (B31.3 Chapt IX) series HP needle valves. COMMUNITIES, LAND & ENVIRONMENT C.R.N. 1. All fittings shall be registered in the name of the Manufacturer.

DATE:

INSPECTION SERVICES SECTION

BOILER/PRESSURE VESSEL BRANCH

Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
 The declaration shall be made by the person having full authority and

 Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.
 CRN expires Sept.28th, 2030 - DG

responsibility for the quality of the end product.



Canadian Registration Number Submittal
Category C: Swagelok Sno-Trik High Pressure Needle Valves

Attachment B. Scope of CRN Registration for Swagelok Sno-Trik 410, 445, 645 and 945 Series High-Pressure Needle Valves (Category C)

This document represents the scope of the Sno-Trik 410, 445, 645 and 945 Series High-Pressure Needle Valves covered by this submission for CRN approval. The 410 Series Valves were designed and evaluated in accordance with ASME B31.1 for unlisted components and ASME B31.3 for unlisted components, while the 445, 645 and 945 High-Pressure Needle Valves were designed and evaluated in accordance with ASME B31.3 Chapter IX for unlisted components.

Summary Table

	Main Pressure Bearing Component	Main Pressure Bearing Material (Standard)	Port Connections and Sizes	Maximum Rated Pressure (psig)		Design Code
Product Series				At -65 to 100°F	At maximum temperature	of Construction
410	Body	316 SS (ASTM A479)	Female NPT 1/4"	15,000	6085 @ 850°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
445	Body	316 SS (ASTM A479)	Swagelok straight thread high-pressure Female 9/16"	45,000	33,400 @ 450°F	ASME B31.3 Chapter IX (Unlisted Components)
			Medium Pressure 1/4"	20,000	18,600 @ 450°F	
645	Body	316 SS (ASTM A479)	Swagelok straight thread high-pressure Female 3/4	45,000	33,400 @ 450°F	
			Medium Pressure 3/8"	20,000	18,600 @ 450°F	
945	Body	316 SS (ASTM A479)	Swagelok straight thread high-pressure Female 1-1/8	45,000	33,400 @ 450°F	
			Medium Pressure 1/2"	20,000	18,600 @ 450°F	

THIS IS PART OF CRN

Date: August 13, 2020

Page 1 of 2

0C22706.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program



Canadian Registration Number Submittal
Category C: Swagelok Sno-Trik High Pressure Needle Valves

Product Illustration



THIS IS PART OF CRN 0C22706.5

Date: August 13, 2020

Page 2 of 2

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

Typical Product Characteristics:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are equal to or less than those shown in the Summary Table. All of the following options are within the scope of this registration:

Stem Material

440C SS S17400 SS

Stem Seal Material

Glass-Filled PTFE Grafoil

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

 Medium and High-Pressure Fittings, Tubing, Valves and Accessories Catalog MS-02-472, Rev M

THIS IS PART OF CRN 0C22706.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)	
29500 Solon Road	348 Bishop Road	
Solon, Ohio 44139	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (Highland)	Swagelok Company (Falon 2)	
318 Bishop Road	358 Bishop Road	
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (OFC)	Swagelok Company (HPF)	
29495 F.A. Lennon Drive	6050 Cochran Road	
Solon, Ohio 44139	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)	
26651 Curtiss Wright Parkway	6060 Cochran Road	
Willoughby Hills, Ohio 44092	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139	
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)	
29900 Solon Industrial Parkway	15400 Foltz Road	
Solon, Ohio 44139	Strongsville, Ohio 44119	
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man	