NEW BRUNSWICK

at a maximum interval of five (5) years.

CRN expires May 14th, 2030 - DG

NOVA SCOTIA

PRINCE EDWARD ISLAND NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

12/23/2019

NUNAVUT MANUFACTURERS NAME: Swagelok Company MANUFACTURERS ADDRESS: 29500 Solon Road, Solon, Ohio 44139 USA PLANT LOCATIONS: Headquarters: 29500 Solon Road, Solon, Ohio 44139 USA (See Attachment A) CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY TITLE OF THE STANDARD OF CONSTRUCTION A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers Rubber Products B Flanges: all flanges C Valves: all line valves Manufacturers (ARPM) DExpansion joints, flexible connections, and hose assemblies: all types Hose Handbook E Strainers, filters, separators, and steam traps F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on bollers, pressure vessels, piping and fusible plugs H Pressure retaining components that do not fall into one of the above categories N Nuclear components: Class 1 □ Class 2 □ Class 3 □, (Meeting AECB or ASME requirements) SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT TYPE OF CONSTRUCTION FORGED | WELDED | WROUGHT | DESCRIBE OTHER: PTFE Core LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED: ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents DECLARATION: [ Joel Feldman, Vice President, Engineering (see note 3) employed by\_ Swagelok Company and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by BSI as being suitable for that purpose and I make this solemn declaration conscientiously, believing it to be true, and knowing that it is of the same force and effect as if made under oath. (19/20/2020 | 7:50 AM EDT Signature of Declarer: Unable to get a notary signature or is space for the Declared before me at day of seal due to COVID-19 situation OFFICIAL SEAL Commissioner of Oaths or Notary Public: (sign) (Affix Official seal to the right) This space for Regulatory Authority use This registration must be revalidated after ten (10) years from the date of acceptance CRN: 0D22419.5 Add1 1214 Addition of Swaged T series PTFE hose assemblies. Notes: 1. All fittings shall be registered in the name of the Manufacturer. 2. Each category shall be supported with two Statutory Declaration 0D22419.5Y ADD1 forms and one copy of supporting documentation. 3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product. 4. Quality control programs shall be resubmitted for validation



Canadian Registration Number Submittal
Category D: Crimped and Swaged T Series PTFE Hose

THIS IS PART OF CRN 0D22419.5ADD1 Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

October 12, 2020 Page 1 of 3

# Attachment B: Scope of Registration for Crimped and Swaged Swagelok T-Series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok PTFE (TH and TC) hose and crimped/swaged assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

## **Summary Table**

TH and	(1 0)					
TC Series Hose Size	At Minimum Temp. (-65°F)	At 65 to 100°F	At Maximum Temp. (450°F)	Pressure Retaining Material	End Connections and Sizes	Design Code of Construction
1/4"	2250	3000	2250	<u>Core</u> Smooth Bore Virgin PTFE [TH]	Swagelok Tube Fitting [SL SM TA TM] 1/8" – 1" (6-25mm)	
3/8"	2250	2500	1875	OR Smooth Bore Carbon-Lined	Male and Female NPT Tapered Pipe Fitting [PM PF] 1/4" – 1"	
1/2"	2000	2000	1500	PTFE [TC]  Braid  304 SS Braid  Reinforcement	Male 37° JIC and Female 37° JIC with female swivel nut [AN AS] 1/4" – 1/2"	Association for Rubber Products Manufacturers (ARPM) Hose
3/4"	1500	1500	1125	End Connections 316 SS Swage Collar	Male and Female ISO/BSP Tapered (ISO 7) Pipe Threads [MT FT] 1/8" – 1"	Handbook
1"	1000	1000	750	304 SS  Crimp on Collar 316 SS	Male and Female VCR Metal Gasket Face Seal Fitting [VF VM] 1/4" – 1"	

#### **Product Description**

Swagelok's TH series hose is virgin PTFE-lined, 304 Stainless Steel braided hose. The TC series hose is carbon black filled PTFE-lined, 304 stainless steel braided hose. All TH and TC series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).



Canadian Registration Number Submittal Category D: Crimped and Swaged T Series PTFE Hose

THIS IS PART OF CRN
0D22419.5ADD1
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety

Program

316 SS end


connections

October 12, 2020 Page 2 of 3

# **Configurations**

Crimped assembly method:


304 SS braid



Swaged assembly method – There are two ways the hose end connections are supplied: Threaded end connection insert or non-threaded end connection insert:

300 series SS

collar





Canadian Registration Number Submittal
Category D: Crimped and Swaged T Series PTFE Hose

THIS IS PART OF CRN 0D22419.5ADD1

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

October 12, 2020 Page 3 of 3

#### **Product Options:**

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

- Polyolefin Cover over Spring-guard
- PVC tubing cover
- Silicone covered Fiber Glass Fire Jacket cover with SS clamps
- Spring guard under Silicone covered Fiber Glass Fire Jacket cover with SS clamps
- SS Tag, TFE Coated SS Lanyard, Aluminum Retaining clamp
- Stainless Steel Tag with TFE coated lanyard
- SS Tag, TFE Coated SS Lanyard, Aluminum Retaining clamp, and possibly pre-swaged
- Customer requested information listed on hose end connection non-critical surfaces
- Applicable material trace numbers marked on end connections.
- Pipe Threaded ends
- O-rings for VCO ends
- Proof Pressure Testing

### **Quality System**

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

#### References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

THIS IS PART OF CRN 0D22419.5ADD1

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

# Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man